

VARISTAR CP STEEL DOOR, PERFORATED WITH 1-POINT LOCKING, RAL 7021, 42 U, 2000H, 600W

KATALOGOVÉ ČÍSLO

21630-006



Varistar CP Perforated Steel Door, IP 20 with Single Point Locking.

VLASTNOSTI

Perforated steel door with single point locking for IP 20 protection class

Opening angle 180°

Key lock cover

VLASTNOSTI PRODUKTU

Product Type: Cabinet Door

Produktová řada: Varistar CP

Typ: Steel Door, Perforated

Works With: Varistar CP

Locking Type: Single Point Locking

Materiál: Steel

Barva: Black Grey

Kód barvy: RAL 7021

Rack Height: 42U

Výška: 2000mm

Šířka: 600mm

Stupeň krytí: IP20

Complies With: IEC 61587-1; IEC 61587-3

ADDITIONAL PRODUCT DETAILS

24U - 33U IP20 doors have 2 hinges, 38U - 52U IP20 doors have 3 hinges to ensure robust IP20 closing structures for taller cabinets

Please order lever handle 24630003 and the DIN lock separately if you want to replace the 1333 DIN lock lever handle

Please purchase the grounding kit separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER