

BASIC PDU, EB0311, 230 VAC, 1-PH, 16 A

KATALOGOVÉ ČÍSLO

EB0311



Modular, compact PDU. Ultra-Low Profile Design

VLASTNOSTI

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 230 VAC, 1-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

VLASTNOSTI PRODUKTU

Product Family: Enlogic

Type: Basic PDU

Product Type: Socket Strip

Socket Type: (12) C13

Socket Quantity: 12

Switched Outlets: No

Circuit Breaker: No Circuit Breaker

Circuit Breaker Quantity: 0

Input Cable Location: Front Feed

Input Current: 16 A

Input Voltage: 200-240 VAC, 1 PH

Interrupt Rating: 5kAIC

Max Power Input: 3.68 kVA

Nominal Voltage: 230V

On/Off Switch Included: No

Output Voltage: 230VAC

Plug Type: IEC 60309 316P6 (IP44)

Rack Units: 1U

Removable Input Cable: Yes

Metering Type: None

Material: Steel

Finish: Powder Coated

Color: Black

Height: 43mm

Width: 444mm

Depth: 41mm

Weight: 2.25kg

Package Quantity: 1

Input Cable Length: 3m

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



nVent.com

TRACER

Our powerful portfolio of brands:

CADDY ERICO HOFFMAN RAYCHEM SCHROFF