

BASIC PDU, EB0450, 400 VAC, 3-PH, 16 A

KATALOGOVÉ ČÍSLO

EB0450



Modular, compact PDU. Ultra-Low Profile Design

VLASTNOSTI

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 400 VAC, 3-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

VLASTNOSTI PRODUKTU

Enlogic

Basic PDU

Socket Strip

(21) C13/C19

Socket Quantity: 42

Switched Outlets: No

Circuit Breaker: No Circuit Breaker

Circuit Breaker Quantity: 0

11A

Input Cable Length: 1.8m

Input Cable Location: Top Feed

Input Current: 16 A / 20 A (16 A derated)

Input Voltage: 380-415 VAC, 3 PH

Max Power Input: 11.5 / 11.0 kVA

Input Voltage: 415V

On/Off Switch Included: No

Output Voltage: 208 – 230VAC

Plug Type: IEC 60309 520P6/516P6

Input/Output: 0U

Removable Input Cable: No

Metering Type: None

Material: Steel

Finish: Powder Coated

Color: Black

Height: 1490mm

Width: 56mm

Depth: 55mm

Weight: 9.5kg

Quantity: 1

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER