

UNIVERSAL SWAY BRACE



The nVent CADDY Universal Sway Brace is an innovative, versatile solution providing seismic bracing for suspended pipes. Featuring a unique slotted hole pattern for easy slip-on installation, installers can eliminate the risk and inconvenience of loose hardware, making it an ideal choice for ensuring safety and compliance on the job.

CERTIFICATIONS



VLASTNOSTI

Used for both lateral and longitudinal sway brace applications

Snap-off bolt head helps enable easy installation and inspection

Works with 1" to 2" (25,4mm to 50,8mm) brace pipes to reduce inventory

Works with 12 gauge or thicker Type A solid strut as brace member

Meets NFPA®-13 and CEN/TS 1755:2021 requirements for seismic sway bracing

FM Approved with the following brace members: Type A Solid Strut (12 gauge or thicker) and 1-2 in Sch40/EN 10255H Pipe

FM Specification Tested with the following brace members: Type A Solid Strut (12 gauge or thicker) and 1-2 in Sch40/EN 10255H Pipe

SPECIFIKACE

Povrchová úprava: Electrogalvanized

Materiál: Steel

Table 1/3

Katalogové číslo	Article Number	Pipe Size, Nominal (Ø)	Pipe Size, Nominal	Cast Iron	NB/DN	Brace Pipe Size
------------------	----------------	------------------------	--------------------	-----------	-------	-----------------

CSB0100N	404101	1in	25.4mm		25	1 – 2in
CSB0125N	404103	1.25in	31.75mm		32	1 – 2in
CSB0400N	404113	4in	101.6mm	101.6mm	100	1 – 2in
CSB0150N	404105	1.5in	38.1mm	38.1mm	40	1 – 2in
CSB0200N	404107	2in	50.8mm	50.8mm	50	1 – 2in
CSB0250N	404109	2.5in	63.5mm	63.5mm	65	1 – 2in
CSB1200	404551	12in	304.8mm	304.8mm	300	1 – 2in
CSB0300N	404111	3in	76.2mm	76.2mm	80	1 – 2in
CSB0500N	404115	5in			125	1 – 2in
CSB1000N	404121	10in	254mm	254mm	250	1 – 2in
CSB1200N	404123	12in	304.8mm	304.8mm	300	1 – 2in
CSB0600N	404117	6in	152.4mm		150	1 – 2in
CSB0800N	404119	8in	203.2mm	203.2mm	200	1 – 2in

Table 2/3						
Katalogové číslo	Article Number	Brace NB/DN	Width (W)	A	C	B
CSB0100N	404101	25 – 50mm	38mm	91mm	16mm	33mm
CSB0125N	404103	25 – 50mm	38mm	91mm	18mm	33mm
CSB0400N	404113	25 – 50mm	38mm	91mm	26mm	33mm
CSB0150N	404105	25 – 50mm	38mm	91mm	19mm	33mm
CSB0200N	404107	25 – 50mm	38mm	91mm	21mm	33mm
CSB0250N	404109	25 – 50mm	38mm	91mm	24mm	33mm
CSB1200	404551	25 – 50mm	38mm	91mm	25mm	33mm
CSB0300N	404111	25 – 50mm	38mm	91mm	25mm	33mm
CSB0500N	404115	25 – 50mm	38mm	91mm	25mm	33mm
CSB1000N	404121	25 – 50mm	38mm	91mm	25mm	33mm
CSB1200N	404123	25 – 50mm	38mm	91mm	25mm	33mm
CSB0600N	404117	25 – 50mm	38mm	91mm	29mm	33mm
CSB0800N	404119	25 – 50mm	38mm	91mm	31mm	33mm

Table 3/3			
Katalogové číslo	Article Number	D	Certifications
CSB0100N	404101	126mm	
CSB0125N	404103	140mm	
CSB0400N	404113	216mm	
CSB0150N	404105	136mm	

Katalogové číslo	Article Number	D	Certifications
CSB0200N	404107	151mm	
CSB0250N	404109	171mm	
CSB1200	404551	429mm	OSHDP/HCAI, FM Approved, Seismic
CSB0300N	404111	187mm	
CSB0500N	404115	255mm	
CSB1000N	404121	386mm	
CSB1200N	404123	429mm	
CSB0600N	404117	275mm	
CSB0800N	404119	331mm	

ADDITIONAL PRODUCT DETAILS

FM® Specification Tested for 1-1/2 in to 4 in pipe sizes using no hub cast iron pipe.

Load ratings for Sch 10 may also be applied to AS 1074 Medium, GB/T 3091, EN 10255 (Medium or Heavy), and JIS G3452 pipe.

Load ratings for Sch 40 may also be applied to AS 1074 Heavy, GB/T 3091, EN 10255 (Heavy), and JIS G3454 pipe.


Load ratings for FM approved lightwall may also be applied to AS 1074 Lightwall, EN 10255 L, EN 10220, and GB/T 8163 pipe.

FM Approved with 12 gauge or thicker Type A solid strut as brace member

UL Loads								
Part Number	Lateral				Longitudinal			
	Sch 10/Sch 40 Service Pipe	Bull Moose Eddy Flow Service Pipe	Wheatland Mega-Flow Service Pipe	Youngstown Fire-Flo Service Pipe	Sch 10/Sch 40 Service Pipe	Bull Moose Eddy Flow Service Pipe	Wheatland Mega-Flow Service Pipe	Youngstown Fire-Flo Service Pipe
CSB0100xxx	8006 N	N/A	N/A	N/A	4448 N	N/A	N/A	N/A
CSB0125xxx	8006 N	8006 N	8006 N	N/A	3025 N	3025 N	3025 N	N/A
CSB0150xxx	8006 N	8006 N	8006 N	8006 N	4448 N	4448 N	4448 N	4448 N
CSB0200xxx	8006 N	8006 N	8006 N	8006 N	5782 N	5782 N	5782 N	5782 N
CSB0250xxx	8006 N	8006 N	8006 N	8006 N	5782 N	5782 N	5782 N	5782 N
CSB0300xxx	8006 N	8006 N	8006 N	8006 N	6227 N	6227 N	6227 N	6227 N
CSB0400xxx	8006 N	8006 N	8006 N	8006 N	7561 N	7561 N	7561 N	7561 N
CSB0500xxx	8006 N	N/A	N/A	N/A	7561 N	N/A	N/A	N/A
CSB0600xxx	8006 N	N/A	8006 N	N/A	7561 N	N/A	7561 N	N/A
CSB0800xxx	8006 N	N/A	N/A	N/A	7561 N	N/A	N/A	N/A
CSB1000xxx	8451 N	N/A	N/A	N/A	8451 N	N/A	N/A	N/A
CSB1200xxx	N/A	N/A	N/A	N/A	N/A	N/A	N/A	N/A

FM Loads								
Part Number	Horizontal Capacity per Installation Angle from Vertical							
	Lateral				Longitudinal			
	30° - 44°	45° - 59°	60° - 74°	75° - 90°	30° - 44°	45° - 59°	60° - 74°	75° - 90°
FM Approved Lightwall, Sch 10 and Sch 40 Service Pipes								
CSB0100xxx	6620 N	9380 N	11470 N	12890 N	5730 N	5510 N	5600 N	6220 N
CSB0125xxx	6130 N	8710 N	10670 N	11960 N	5730 N	5510 N	5600 N	6220 N
CSB0150xxx	6130 N	8710 N	10670 N	11960 N	5330 N	8270 N	9690 N	10000 N
CSB0200xxx	6130 N	8710 N	10670 N	11960 N	5330 N	8090 N	9690 N	10000 N
CSB0250xxx	6400 N	9020 N	11070 N	12410 N	5870 N	8090 N	9740 N	11120 N
CSB0300xxx	6180 N	8760 N	10760 N	12050 N	5780 N	7960 N	9740 N	11120 N
CSB0400xxx	6180 N	8760 N	10760 N	12050 N	5780 N	7960 N	9740 N	11120 N
CSB0500xxx	6180 N	8760 N	10760 N	12050 N	5780 N	7960 N	9740 N	11120 N
CSB0600xxx	6490 N	9160 N	11200 N	12580 N	6270 N	8670 N	10450 N	11920 N
0.188" Wall and Sch 40 Service Pipes								
CSB0800xxx	5910 N	8360 N	10230 N	11470 N	6220 N	8540 N	10450 N	11740 N
CSB1000xxx	5910 N	8360 N	10230 N	11470 N	6220 N	8540 N	10450 N	11740 N
CSB1200xxx	7470 N	10540 N	12940 N	14500 N	7110 N	8270 N	9960 N	11520 N

DIAGRAMS



UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER