

VARISTAR CP SERVER CABINET



Welded steel frame for high static load requirements. Prepared for 19" integration of IT assets.

VLASTNOSTI

Preconfigured, ready to use cabinet

Static load-carrying capacity up to 1600 kg, dynamic 1000 kg

Ingress protection class IP 20

Installation of different IT equipment possible

Integrated air panels for front to back cooling

Can be easily integrated into aisle containment system

SPECIFIKACE

Table 1/3

Katalogové číslo	Typ	Cladding Material	Frame Material	Cladding Color	Cladding Color Code	Static Load
10630-017	Standard	Steel	Steel	Black Grey	RAL 7021	1600kgf
10630-018	Standard	Steel	Steel	Black Grey	RAL 7021	1600kgf
10630-019	Standard	Steel	Steel	Black Grey	RAL 7021	1600kgf
10630-020	Standard	Steel	Steel	Black Grey	RAL 7021	1600kgf
10630-023	Side-by-Side	Steel	Steel	Black Grey	RAL 7021	1600kgf
10630-024	Side-by-Side	Steel	Steel	Black Grey	RAL 7021	1600kgf

Katalogové číslo	Typ	Cladding Material	Frame Material	Cladding Color	Cladding Color Code	Static Load
10630-025	Side-by-Side	Steel	Steel	Black Grey	RAL 7021	1600kgf
10630-026	Side-by-Side	Steel	Steel	Black Grey	RAL 7021	1600kgf

Table 2/3

Katalogové číslo	Dynamic Load	Product Type	Výška	Rack Height	Množství v balení	Povrchová úprava
10630-017	1000kgf	Rack	2000mm	42U	1	Powder Coated
10630-018	1000kgf	Rack	2000mm	42U	1	Powder Coated
10630-019	1000kgf	Rack	2200mm	47U	1	Powder Coated
10630-020	1000kgf	Rack	2200mm	47U	1	Powder Coated
10630-023	1000kgf	Rack	2000mm	42U	1	Powder Coated
10630-024	1000kgf	Rack	2000mm	42U	1	Powder Coated
10630-025	1000kgf	Rack	2200mm	47U	1	Powder Coated
10630-026	1000kgf	Rack	2200mm	47U	1	Powder Coated

Table 3/3

Katalogové číslo	Materiál	Šířka	Hloubka
10630-017	Steel	600mm	1200mm
10630-018	Steel	800mm	1200mm
10630-019	Steel	600mm	1200mm
10630-020	Steel	800mm	1200mm
10630-023	Steel	600mm	1200mm
10630-024	Steel	800mm	1200mm
10630-025	Steel	600mm	1200mm
10630-026	Steel	800mm	1200mm

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER