

## FRONT PANEL, FRONT SHIELDED, SIDE HINGED

Front panel with textile EMC gasket, side hinged assembly.



### CERTIFICATIONS



### VLASTNOSTI

Front panel with textile EMC gasket

Enables mounting onto the horizontal rails

Suitable for sub racks and cases

Hinges can be fitted on left or right

### SPECIFIKACE

**Accessory Type:** Front panel

Table 1/3

| Katalogové číslo | Typ                        | Mounting     | EMC Shielding      | EMC Gasket Type | Materiál | Front Finish |
|------------------|----------------------------|--------------|--------------------|-----------------|----------|--------------|
| 20848-611        | Front Panel without Handle | Hinged, Side | No (Retrofittable) | Textile         | Aluminum | Anodized     |
| 20848-617        | Front Panel without Handle | Hinged, Side | No (Retrofittable) | Textile         | Aluminum | Anodized     |

| Table 2/3        |             |               |             |           |            |           |
|------------------|-------------|---------------|-------------|-----------|------------|-----------|
| Katalogové číslo | Rear Finish | Treated Edges | Rack Height | Výška (H) | Rack Width | Šířka (W) |
| 20848-611        | Conductive  | No            | 3U          | 128.4mm   | 84HP       | 426.4mm   |
| 20848-617        | Conductive  | No            | 6U          | 261.8mm   | 84HP       | 426.4mm   |

| Katalogové číslo | Hloubka (D) | Množství v balení | Povrchová úprava     |
|------------------|-------------|-------------------|----------------------|
| 20848-611        | 2.5mm       | 1                 | Anodized, Passivated |
| 20848-617        | 2.5mm       | 1                 | Anodized, Passivated |

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na [www.nvent.com](http://www.nvent.com) a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

All locations  
+1.763.422.2661  
Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)

Straubenhardt, Germany  
 +49.7082.794.0  
 Betschdorf, France  
 +33.3.88.90.64.90  
 Warsaw, Poland  
 +48.22.209.98.35  
 Assago, Italy  
 +39.02.932.7141  
 Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[schroff.nvent.com](http://schroff.nvent.com)

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[schroff.nvent.com](https://schroff.nvent.com)



**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER**