

PMC MEZZANINE FRONT PANEL, UNTREATED, WITH EMC SHIELDING



Mezzanine front panel is fitted into PMC front panel cut-outs.
Available in different treatments. For O-ring EMC gasket.

CERTIFICATIONS



VLASTNOSTI

Mezzanine front panel is fitted into PMC front panel cut-outs

EMC shielding with conductive O-ring

SPECIFIKACE

Accessory Type: Front panel

Table 1/3

Katalogové číslo	Typ	Mounting	EMC Shielding	EMC Gasket Type	Materiál	Front Finish
20835-598	Front Panel without Handle	Screw-on Front	Yes	O-ring	Aluminum	Anodized
20835-889	Front Panel without Handle	Screw-on Front	Yes	O-ring	Aluminum	Anodized
20835-890	Front Panel without Handle	Screw-on Front	Yes		Zinc	
20835-922	Front Panel without Handle	Screw-on Front	Yes		Zinc	Chrome Plated

Katalogové číslo	Typ	Mounting	EMC Shielding	EMC Gasket Type	Materiál	Front Finish
20835-923	Front Panel without Handle	Screw-on Front	Yes		Zinc	Chrome Plated
20835-893	Front Panel without Handle	Screw-on Front	Yes		Zinc	Chrome Plated
20835-924	Front Panel without Handle	Screw-on Front	Yes		Zinc	Chrome Plated
20835-928	Front Panel without Handle	Screw-on Front	Yes		Zinc	Anodized

Table 2/3						
Katalogové číslo	Rear Finish	Treated Edges	Výška	Šířka	Hloubka	Complies With
20835-598	Conductive	No	74mm	12.7mm	2.5mm	PMC Mezzanine, IEEE P1386
20835-889	Conductive	No	74mm	12.7mm	2.5mm	PMC Mezzanine, IEEE P1386
20835-890		No	74mm	12.7mm		PMC Mezzanine, IEEE P1386
20835-922	Chrome Plated	Yes	74mm	12.7mm		PMC Mezzanine, IEEE P1386
20835-923	Chrome Plated	Yes	74mm	12.7mm		PMC Mezzanine, IEEE P1386
20835-893	Chrome Plated	Yes	74mm	12.7mm		PMC Mezzanine, IEEE P1386
20835-924	Chrome Plated	Yes	74mm	12.7mm		PMC Mezzanine, IEEE P1386
20835-928	Conductive	No	74mm	12.7mm		PMC Mezzanine, IEEE P1386

Table 3/3		
Katalogové číslo	Množství v balení	Povrchová úprava
20835-598	1	Anodized
20835-889	1	Anodized
20835-890	1	
20835-922	1	
20835-923	1	
20835-893	10	
20835-924	10	
20835-928	10	

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER