

SOCKET STRIP, IEC C13, WITH WIELAND® INPUT



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

CERTIFICATIONS



VLASTNOSTI

Input via Wieland® GST 18 plug

Installation height 1 U

In accordance with IEC 60320

Horizontal or vertical mounting

Output via IEC 60320 C-13 sockets

Socket strips can be rotated through all four directions (in 90° increments) during fitting

SPECIFIKACE

Table 1/2

Katalogové číslo	Product Type	Typ zásuvky	Socket Quantity	Switched Outlets	Barva	Napětí střídavé
60110-340	Socket Strip	IEC C13	12	No	Grey	230V
60110-341	Socket Strip	IEC C13	12	No	Black	230V
60110-342	Socket Strip	IEC C13	12	No	Red	230V
60110-349	Socket Strip	IEC C13	6	No	Grey	230V

Katalogové číslo	ProductType	Typ zásuvky	Socket Quantity	Switched Outlets	Barva	Napětí střídavé
60110-350	Socket Strip	IEC C13	6	No	Black	230V
60110-351	Socket Strip	IEC C13	6	No	Red	230V

Table 2/2						
Katalogové číslo	Function	Length	Hloubka	Materiál	Povrchová úprava	Množství v balení
60110-340		438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-341		438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-342		438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-349	Overcurrent Protection	438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-350	Overcurrent Protection	438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-351	Overcurrent Protection	438.5mm	44mm	Aluminum, Polyamide	Anodized	1

ADDITIONAL PRODUCT DETAILS

Please order mounting bracket for vertical mounting separately.

UPOZORNĚNÍ

Produkty nVent musí být instalovány a používány pouze tak, jak je uvedeno v instrukčních listech a materiálech pro školení nVent. Instrukční listy jsou k dispozici na www.nvent.com a od vašeho zástupce zákaznického servisu nVent. Nesprávná instalace, zneužití, nesprávné použití nebo jiný nedostatek úplného dodržování pokynů a varování nVent může způsobit selhání produktu, poškození majetku, vážné zranění osob a smrt a/nebo zrušit vaši záruku.

North America

All locations

+1.763.422.2661

Chat with us:

schroff.nvent.com

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

schroff.nvent.com

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

schroff.nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER