

19" FAN UNIT, 1 U, SPEED CONTROL AND MONITORING

Fan Unit for installation into a 1 U space within the Cabinet.



CERTIFICATIONS



MERKMALE

- Range selectable: 20 ... 40 °C and 30 ... 50 °C
- Low noise through temperature dependent air flow
- External sensor, max speed is default failure state
- Function control with LEDs and via dry contact
- Contact protection in accordance with DIN EN ISO 13857

SPEZIFIKATIONEN

Table 1/1

Katalognummer	Input Voltage DC	Product Type	Input Voltage AC	Zubehörtyp	Zertifizierungen
10713-098	24 V min	Fan Unit		Fan unit, 19"	RoHS, CE, EAC
10713-099	24 V min	Fan Unit		Fan unit, 19"	RoHS, CE, EAC
19713-006		Fan Unit	230 V min	Fan unit, 19"	RoHS, EAC
19713-121		Fan Unit	230 V min	Fan unit, 19"	RoHS, EAC

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER