

FRONT PANEL, ANODIZED, UNSHIELDED, SCREW ASSEMBLY

Anodized front panel, unshielded version, Al, 2.5 mm.



CERTIFICATIONS



MERKMALE

Partial width front panel, Al, 2.5 mm

Al, anodized

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width	Package Quantity
30807-416	Ja	Anodized	Anodized	Nein	84 HP	1
30807-494	Ja	Anodized	Anodized	Nein	42 HP	1
30807-506	Ja	Anodized	Anodized	Nein	84 HP	1
30807-596	Ja	Anodized	Anodized	Nein	84 HP	1
30807-764	Ja	Anodized	Anodized	Nein	42 HP	1
30807-771	Ja	Anodized	Anodized	Nein	63 HP	1
30807-776	Ja	Anodized	Anodized	Nein	84 HP	1
30808-067	Ja	Anodized	Anodized	Nein	63 HP	1

Katalognummer	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width	Package Quantity
30810-432	Ja	Anodized	Anodized	Nein	2 HP	5
30818-741	Nein	Anodized	Conductive	Nein	2 HP	5
30807-481	Ja	Anodized	Anodized	Nein	4 HP	5
30807-482	Ja	Anodized	Anodized	Nein	6 HP	5
30807-483	Ja	Anodized	Anodized	Nein	10 HP	5
30807-484	Ja	Anodized	Anodized	Nein	8 HP	5
30807-485	Ja	Anodized	Anodized	Nein	12 HP	5
30807-487	Ja	Anodized	Anodized	Nein	21 HP	5
30807-496	Ja	Anodized	Anodized	Nein	28 HP	5
30807-501	Ja	Anodized	Anodized	Nein	14 HP	5
30807-508	Ja	Anodized	Anodized	Nein	3 HP	5
30807-509	Ja	Anodized	Anodized	Nein	7 HP	5
30807-510	Ja	Anodized	Anodized	Nein	5 HP	5
30807-778	Ja	Anodized	Anodized	Nein	4 HP	5
30807-777	Ja	Anodized	Anodized	Nein	5 HP	5
30807-752	Ja	Anodized	Anodized	Nein	6 HP	5
30807-753	Ja	Anodized	Anodized	Nein	10 HP	5
30807-755	Ja	Anodized	Anodized	Nein	12 HP	5
30807-757	Ja	Anodized	Anodized	Nein	21 HP	5
30807-758	Ja	Anodized	Conductive	Nein	14 HP	5
30807-766	Ja	Anodized	Anodized	Nein	28 HP	5
30807-779	Ja	Anodized	Anodized	Nein	8 HP	5
30807-780	Ja	Anodized	Anodized	Nein	16 HP	5
30807-833	Ja	Anodized	Anodized	Nein	7 HP	

Table 2/3						
Katalognummer	Höhe	Product Type	Typ	Rack Height	Breite	Konform mit
30807-416	84 mm	Frontplatte	Front Panel without Handle	2 U	426.4 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-494	128.4 mm	Frontplatte	Front Panel without Handle	3 U	213 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-506	128.4 mm	Frontplatte	Front Panel without Handle	3 U	426.4 mm	IEC 60297-3-101, IEEE 1101.1/10

Katalognummer	Höhe	ProductType	Typ	Rack Height	Breite	Konform mit
30807-596	172.9 mm	Frontplatte	Front Panel without Handle	4 U	426.4 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-764	261.8 mm	Frontplatte	Front Panel without Handle	6 U	213 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-771	261.8 mm	Frontplatte	Front Panel without Handle	6 U	319.7 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-776	261.8 mm	Frontplatte	Front Panel without Handle	6 U	426.4 mm	IEC 60297-3-101, IEEE 1101.1/10
30808-067	128.4 mm	Frontplatte	Front Panel without Handle	3 U	319.7 mm	IEC 60297-3-101, IEEE 1101.1/10
30810-432	128.4 mm	Frontplatte	Front Panel without Handle	3 U	9.8 mm	IEC 60297-3-101, IEEE 1101.1/10
30818-741	261.8 mm	Frontplatte	Front Panel without Handle	6 U	9.8 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-481	128.4 mm	Frontplatte	Front Panel without Handle	3 U	20 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-482	128.4 mm	Frontplatte	Front Panel without Handle	3 U	30.1 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-483	128.4 mm	Frontplatte	Front Panel without Handle	3 U	50.5 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-484	128.4 mm	Frontplatte	Front Panel without Handle	3 U	40.3 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-485	128.4 mm	Frontplatte	Front Panel without Handle	3 U	60.6 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-487	128.4 mm	Frontplatte	Front Panel without Handle	3 U	106.3 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-496	128.4 mm	Frontplatte	Front Panel without Handle	3 U	141.9 mm	IEC 60297-3-101, IEEE 1101.1/10

Katalognummer	Höhe	ProductType	Typ	Rack Height	Breite	Konform mit
30807-501	128.4 mm	Frontplatte	Front Panel without Handle	3 U	70.8 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-508	128.4 mm	Frontplatte	Front Panel without Handle	3 U	14.9 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-509	128.4 mm	Frontplatte	Front Panel without Handle	3 U	35.2 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-510	128.4 mm	Frontplatte	Front Panel without Handle	3 U	25 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-778	261.8 mm	Frontplatte	Front Panel without Handle	6 U	20 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-777	261.8 mm	Frontplatte	Front Panel without Handle	6 U	25 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-752	261.8 mm	Frontplatte	Front Panel without Handle	6 U	30.1 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-753	261.8 mm	Frontplatte	Front Panel without Handle	6 U	50.5 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-755	261.8 mm	Frontplatte	Front Panel without Handle	6 U	60.6 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-757	261.8 mm	Frontplatte	Front Panel without Handle	6 U	106.3 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-758	261.8 mm	Frontplatte	Front Panel without Handle	6 U	70.8 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-766	261.8 mm	Frontplatte	Front Panel without Handle	6 U	141.9 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-779	261.8 mm	Frontplatte	Front Panel without Handle	6 U	40.3 mm	IEC 60297-3-101, IEEE 1101.1/10
30807-780	261.8 mm	Frontplatte	Front Panel without Handle	6 U	80.9 mm	IEC 60297-3-101, IEEE 1101.1/10

Katalognummer	Höhe	ProductType	Typ	Rack Height	Breite	Konform mit
30807-833	261.8 mm	Frontplatte	Front Panel without Handle	6 U	35.2 mm	IEC 60297-3-101, IEEE 1101.1/10

Table 3/3			
Katalognummer	Montage	Material	Zertifizierungen
30807-416	Screw-on Front	Aluminium	RoHS
30807-494	Screw-on Front	Aluminium	RoHS
30807-506	Screw-on Front	Aluminium	RoHS
30807-596	Screw-on Front	Aluminium	
30807-764	Screw-on Front	Aluminium	RoHS
30807-771	Screw-on Front	Aluminium	RoHS
30807-776	Screw-on Front	Aluminium	RoHS
30808-067	Screw-on Front	Aluminium	RoHS
30810-432	Screw-on Front	Aluminium	RoHS
30818-741	Screw-on Front	Aluminium	RoHS
30807-481	Screw-on Front	Aluminium	RoHS
30807-482	Screw-on Front	Aluminium	RoHS
30807-483	Screw-on Front	Aluminium	RoHS
30807-484	Screw-on Front	Aluminium	RoHS
30807-485	Screw-on Front	Aluminium	RoHS
30807-487	Screw-on Front	Aluminium	RoHS
30807-496	Screw-on Front	Aluminium	RoHS
30807-501	Screw-on Front	Aluminium	RoHS
30807-508	Screw-on Front	Aluminium	RoHS
30807-509	Screw-on Front	Aluminium	RoHS
30807-510	Screw-on Front	Aluminium	RoHS
30807-778	Screw-on Front	Aluminium	RoHS
30807-777	Screw-on Front	Aluminium	RoHS
30807-752	Screw-on Front	Aluminium	RoHS
30807-753	Screw-on Front	Aluminium	RoHS
30807-755	Screw-on Front	Aluminium	RoHS
30807-757	Screw-on Front	Aluminium	RoHS
30807-758	Screw-on Front	Aluminium	RoHS
30807-766	Screw-on Front	Aluminium	RoHS

Katalognummer	Montage	Material	Zertifizierungen
30807-779	Screw-on Front	Aluminium	RoHS
30807-780	Screw-on Front	Aluminium	RoHS
30807-833	Screw-on Front	Aluminium	RoHS

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER