

VARISTAR CP FRAME

Varistar welded steel frame for static load requirements. For 19", ETSI or mounting plate integration.

MERKMALE

Welded, finish powder-coated, black gray, RAL 7021

St, 1.5 mm, zinc-plated, with central GND/grounding point

Static load-carrying capacity max. 1600 kg

Please order adjustable feet separately

SPEZIFIKATIONEN

Table 1/3

Katalognummer	Frame Material	Höhe	Product Type	Product Family	Kompatibel mit	Typ
20630-065	Stahl	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-066	Stahl	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-067	Stahl	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-068	Stahl	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-071	Stahl	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-072	Stahl	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-073	Stahl	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-074	Stahl	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-075	Stahl	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-076	Stahl	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard

Katalognummer	Frame Material	Höhe	ProductType	Product Family	Kompatibel mit	Typ
20630-077	Stahl	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-078	Stahl	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-079	Stahl	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-080	Stahl	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-081	Stahl	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-082	Stahl	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-083	Stahl	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-084	Stahl	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-085	Stahl	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-086	Stahl	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-087	Stahl	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-088	Stahl	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-089	Stahl	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-090	Stahl	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-091	Stahl	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-092	Stahl	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-093	Stahl	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-094	Stahl	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-095	Stahl	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-096	Stahl	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard

Katalognummer	Frame Material	Höhe	ProductType	Product Family	Kompatibel mit	Typ
20630-097	Stahl	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-098	Stahl	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-099	Stahl	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-100	Stahl	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-101	Stahl	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-102	Stahl	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-103	Stahl	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-104	Stahl	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-105	Stahl	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-106	Stahl	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-107	Stahl	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-108	Stahl	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-109	Stahl	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-110	Stahl	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-261	Stahl	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-111	Stahl	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-112	Stahl	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-113	Stahl	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-114	Stahl	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-115	Stahl	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard

Katalognummer	Frame Material	Höhe	ProductType	Product Family	Kompatibel mit	Typ
20630-116	Stahl	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-117	Stahl	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-118	Stahl	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-119	Stahl	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-120	Stahl	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-121	Stahl	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-122	Stahl	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-262	Stahl	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-123	Stahl	2450 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-124	Stahl	2450 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-125	Stahl	2450 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-126	Stahl	2450 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-127	Stahl	2450 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-128	Stahl	2450 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard

Table 2/3						
Katalognummer	Rack Height	Breite	Konform mit	Tiefe	Farbe	Material
20630-065	24 U	600 mm		600 mm	Black Grey	Stahl
20630-066	24 U	600 mm		800 mm	Black Grey	Stahl
20630-067	24 U	600 mm		900 mm	Black Grey	Stahl
20630-068	24 U	600 mm		1000 mm	Black Grey	Stahl
20630-071	24 U	800 mm		600 mm	Black Grey	Stahl
20630-072	24 U	800 mm		800 mm	Black Grey	Stahl
20630-073	24 U	800 mm		900 mm	Black Grey	Stahl
20630-074	24 U	800 mm		1000 mm	Black Grey	Stahl

Katalognummer	Rack Height	Breite	Konform mit	Tiefe	Farbe	Material
20630-075	29 U	600 mm		600 mm	Black Grey	Stahl
20630-076	29 U	600 mm		800 mm	Black Grey	Stahl
20630-077	29 U	600 mm		900 mm	Black Grey	Stahl
20630-078	29 U	600 mm		1000 mm	Black Grey	Stahl
20630-079	29 U	800 mm		600 mm	Black Grey	Stahl
20630-080	29 U	800 mm		800 mm	Black Grey	Stahl
20630-081	29 U	800 mm		900 mm	Black Grey	Stahl
20630-082	29 U	800 mm		1000 mm	Black Grey	Stahl
20630-083	33 U	600 mm		600 mm	Black Grey	Stahl
20630-084	33 U	600 mm		800 mm	Black Grey	Stahl
20630-085	33 U	600 mm		900 mm	Black Grey	Stahl
20630-086	33 U	600 mm		1000 mm	Black Grey	Stahl
20630-087	33 U	800 mm		600 mm	Black Grey	Stahl
20630-088	33 U	800 mm		800 mm	Black Grey	Stahl
20630-089	33 U	800 mm		900 mm	Black Grey	Stahl
20630-090	33 U	800 mm		1000 mm	Black Grey	Stahl
20630-091	38 U	600 mm		600 mm	Black Grey	Stahl
20630-092	38 U	600 mm		800 mm	Black Grey	Stahl
20630-093	38 U	600 mm		900 mm	Black Grey	Stahl
20630-094	38 U	600 mm		1000 mm	Black Grey	Stahl
20630-095	38 U	800 mm		600 mm	Black Grey	Stahl
20630-096	38 U	800 mm		800 mm	Black Grey	Stahl
20630-097	38 U	800 mm		900 mm	Black Grey	Stahl
20630-098	38 U	800 mm		1000 mm	Black Grey	Stahl
20630-099	42 U	600 mm		600 mm	Black Grey	Stahl
20630-100	42 U	600 mm		800 mm	Black Grey	Stahl
20630-101	42 U	600 mm		900 mm	Black Grey	Stahl
20630-102	42 U	600 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Stahl
20630-103	42 U	600 mm	IEC 61587-1, IEC 61587-3	1100 mm	Black Grey	Stahl
20630-104	42 U	600 mm	IEC 61587-1, IEC 61587-3	1200 mm	Black Grey	Stahl
20630-105	42 U	800 mm		600 mm	Black Grey	Stahl
20630-106	42 U	800 mm		800 mm	Black Grey	Stahl

Katalognummer	Rack Height	Breite	Konform mit	Tiefe	Farbe	Material
20630-107	42 U	800 mm		900 mm	Black Grey	Stahl
20630-108	42 U	800 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Stahl
20630-109	42 U	800 mm	IEC 61587-1, IEC 61587-3	1100 mm	Black Grey	Stahl
20630-110	42 U	800 mm	IEC 61587-1, IEC 61587-3	1200 mm	Black Grey	Stahl
20630-261	42 U	600 mm		300 mm	Black Grey	Stahl
20630-111	47 U	600 mm		600 mm	Black Grey	Stahl
20630-112	47 U	600 mm		800 mm	Black Grey	Stahl
20630-113	47 U	600 mm		900 mm	Black Grey	Stahl
20630-114	47 U	600 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Stahl
20630-115	47 U	600 mm	IEC 61587-1, IEC 61587-3	1100 mm	Black Grey	Stahl
20630-116	47 U	600 mm	IEC 61587-1, IEC 61587-3	1200 mm	Black Grey	Stahl
20630-117	47 U	800 mm		600 mm	Black Grey	Stahl
20630-118	47 U	800 mm		800 mm	Black Grey	Stahl
20630-119	47 U	800 mm		900 mm	Black Grey	Stahl
20630-120	47 U	800 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Stahl
20630-121	47 U	800 mm	IEC 61587-1, IEC 61587-3	1100 mm	Black Grey	Stahl
20630-122	47 U	800 mm	IEC 61587-1, IEC 61587-3	1200 mm	Black Grey	Stahl
20630-262	47 U	600 mm		300 mm	Black Grey	Stahl
20630-123	52 U	600 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Stahl
20630-124	52 U	600 mm	IEC 61587-1, IEC 61587-3	1100 mm	Black Grey	Stahl
20630-125	52 U	600 mm	IEC 61587-1, IEC 61587-3	1200 mm	Black Grey	Stahl
20630-126	52 U	800 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Stahl
20630-127	52 U	800 mm	IEC 61587-1, IEC 61587-3	1100 mm	Black Grey	Stahl
20630-128	52 U	800 mm	IEC 61587-1, IEC 61587-3	1200 mm	Black Grey	Stahl

Table 3/3

Katalognummer	Color Code	Statische Last
20630-065	RAL 7021	
20630-066	RAL 7021	
20630-067	RAL 7021	
20630-068	RAL 7021	
20630-071	RAL 7021	
20630-072	RAL 7021	
20630-073	RAL 7021	
20630-074	RAL 7021	
20630-075	RAL 7021	
20630-076	RAL 7021	
20630-077	RAL 7021	
20630-078	RAL 7021	
20630-079	RAL 7021	
20630-080	RAL 7021	
20630-081	RAL 7021	
20630-082	RAL 7021	
20630-083	RAL 7021	
20630-084	RAL 7021	
20630-085	RAL 7021	
20630-086	RAL 7021	
20630-087	RAL 7021	
20630-088	RAL 7021	
20630-089	RAL 7021	
20630-090	RAL 7021	
20630-091	RAL 7021	
20630-092	RAL 7021	
20630-093	RAL 7021	
20630-094	RAL 7021	
20630-095	RAL 7021	
20630-096	RAL 7021	
20630-097	RAL 7021	
20630-098	RAL 7021	
20630-099	RAL 7021	
20630-100	RAL 7021	

Katalognummer	Color Code	Statische Last
20630-101	RAL 7021	
20630-102	RAL 7021	1600 kgf
20630-103	RAL 7021	1600 kgf
20630-104	RAL 7021	1600 kgf
20630-105	RAL 7021	
20630-106	RAL 7021	
20630-107	RAL 7021	
20630-108	RAL 7021	1600 kgf
20630-109	RAL 7021	1600 kgf
20630-110	RAL 7021	1600 kgf
20630-261	RAL 7021	
20630-111	RAL 7021	
20630-112	RAL 7021	
20630-113	RAL 7021	
20630-114	RAL 7021	1600 kgf
20630-115	RAL 7021	1600 kgf
20630-116	RAL 7021	1600 kgf
20630-117	RAL 7021	
20630-118	RAL 7021	
20630-119	RAL 7021	
20630-120	RAL 7021	1600 kgf
20630-121	RAL 7021	1600 kgf
20630-122	RAL 7021	1600 kgf
20630-262	RAL 7021	
20630-123	RAL 7021	1600 kgf
20630-124	RAL 7021	1600 kgf
20630-125	RAL 7021	1600 kgf
20630-126	RAL 7021	1600 kgf
20630-127	RAL 7021	1600 kgf
20630-128	RAL 7021	1600 kgf

ADDITIONAL PRODUCT DETAILS

A combination of castors and castors with adjustable feet is not possible with the standard frame. Please order the mobile frame for this requirement

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER