

19" FAN UNIT, 1 U, REMOTE CONTROL AND MONITORING

Fan Unit with ModBus interface for installation into a 1 U space within the Cabinet

MERKMALE

Fan speed temperature controlled

ModBus Interface for Remote Monitoring and Control

Temperature threshold for the fan control adjustable on the front panel

Signaling of fan failure and over temperature by 2 LEDs and potential-free relay outputs

Integrated power supply with wide range input (100 V – 240 V)

Less than 1 U (42 mm) to enable mounting on sliding guide rails or drawer

2 NTC temperature sensors with Cables included

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Airflow	Noise Level	Strom	Max Static Pressure	Umgebungstemperatur	Lifespan, L10 @ 40 C
10713-554	1089 m³/h	59.5 dB(A)	97 W	78 Pa	-10 to 70 °C	99558 h

Table 2/2

Katalognummer	Product Type	Input Voltage AC
10713-554	Fan Unit	100 – 240 V

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER