

19" FAN UNIT, 1 U, SPEED CONTROL AND MONITORING

Fan Unit for installation into a 1 U space within the Cabinet.



CERTIFICATIONS



MERKMALE

Range selectable: 20 ... 40 °C and 30 ... 50 °C

Low noise through temperature dependent air flow

External sensor, max speed is default failure state

Function control with LEDs and via dry contact

Contact protection in accordance with DIN EN ISO 13857

SPEZIFIKATIONEN

Table 1/1

Katalognummer	Input Voltage DC	Product Type	Input Voltage AC	Zubehörtyp	Zertifizierungen
10713-098	24 V min	Fan Unit		Fan unit, 19"	RoHS, CE, EAC
10713-099	24 V min	Fan Unit		Fan unit, 19"	RoHS, CE, EAC
19713-006		Fan Unit	230 V min	Fan unit, 19"	RoHS, EAC
19713-121		Fan Unit	230 V min	Fan unit, 19"	RoHS, EAC

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER