

GUIDE RAIL WITH CODING, PREASSEMBLED ESD CLIP FOR COMPACTPCI/ VME64X, PC

MERKMALE

NEW generation with coding type plastic guide rails for reliable retention of PCBs or plug-in units

Significantly increased stability, due to an optimized design and high quality material (PC)

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted to the horizontal rails Type H and R for higher shock and vibration requirements

ESD clip for an conductive contact between PCB and horizontal rail preassembled

Storage temperature: from -40 °C ... 130 °C

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Board Depth	Package Quantity	Product Type	Product Family	Kompatibel mit	Typ
24568-847	160 mm	10	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Sub racks, Cases, 19" Chassis, Systems	With Coding and preassembled ESD Clips
24568-848	160 mm	10	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Sub racks, Cases, 19" Chassis, Systems	With Coding and preassembled ESD Clips

Katalognummer	Board Depth	Package Quantity	ProductType	Product Family	Kompatibel mit	Typ
24568-850	160 mm	10	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, 19" Chassis, Systems	With Coding and preassembled ESD Clips
24568-851	160 mm	10	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, 19" Chassis, Systems	With Coding and preassembled ESD Clips
24568-853	70 mm	10	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, 19" Chassis, Systems	With Coding and preassembled ESD Clips
24568-854	70 mm	10	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, 19" Chassis, Systems	With Coding and preassembled ESD Clips
24568-855	70 mm	10	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, 19" Chassis, Systems	With Coding and preassembled ESD Clips
24568-856	70 mm	10	Guide Rail	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Subracks, Cases, 19" Chassis, Systems	With Coding and preassembled ESD Clips

Table 2/2

Katalognummer	Konform mit	Farbe	Material	Groove Width
24568-847	EN 45545-2	Rot	Polykarbonat	2
24568-848	EN 45545-2	Grau	Polykarbonat	2
24568-850	EN 45545-2	Rot	Polykarbonat	2
24568-851	EN 45545-2	Grau	Polykarbonat	2
24568-853	EN 45545-2	Rot	Polykarbonat	2
24568-854	EN 45545-2	Grau	Polykarbonat	2
24568-855	EN 45545-2	Rot	Polykarbonat	2
24568-856	EN 45545-2	Grau	Polykarbonat	2

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER