

SOCKET STRIP, IEC C13, WITH WIELAND® INPUT



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

CERTIFICATIONS



MERKMALE

Input via Wieland® GST 18 plug

Installation height 1 U

In accordance with IEC 60320

Horizontal or vertical mounting

Output via IEC 60320 C-13 sockets

Socket strips can be rotated through all four directions (in 90° increments) during fitting

SPEZIFIKATIONEN

Table 1/2

Katalognummer	Wechselspannung	Product Type	Socket Type	Funktion	Tiefe	Farbe
60110-340	230 V	Socket Strip	IEC C13		44 mm	Grau
60110-341	230 V	Socket Strip	IEC C13		44 mm	Schwarz
60110-342	230 V	Socket Strip	IEC C13		44 mm	Rot
60110-349	230 V	Socket Strip	IEC C13	Overcurrent Protection	44 mm	Grau

Katalognummer	Wechselspannung	ProductType	Socket Type	Funktion	Tiefe	Farbe
60110-350	230 V	Socket Strip	IEC C13	Overcurrent Protection	44 mm	Schwarz
60110-351	230 V	Socket Strip	IEC C13	Overcurrent Protection	44 mm	Rot

Table 2/2

Katalognummer	Länge
60110-340	438.5 mm
60110-341	438.5 mm
60110-342	438.5 mm
60110-349	438.5 mm
60110-350	438.5 mm
60110-351	438.5 mm

ADDITIONAL PRODUCT DETAILS

Please order mounting bracket for vertical mounting separately.

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER