

FRONT PANEL, FRONT SHIELDED, SIDE HINGED

Front panel with textile EMC gasket, side hinged assembly.



CERTIFICATIONS



MERKMALE

Front panel with textile EMC gasket

Enables mounting onto the horizontal rails

Suitable for subracks and cases

Hinges can be fitted on left or right

SPEZIFIKATIONEN

Table 1/3

Katalognummer	EMC Gasket Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
20848-611	Textile	Nein	Anodized	Conductive	No (Retrofittable)	84 HP
20848-617	Textile	Nein	Anodized	Conductive	No (Retrofittable)	84 HP

Table 2/3

Katalognummer	Package Quantity	Höhe	Product Type	Typ	Rack Height	Breite
---------------	------------------	------	--------------	-----	-------------	--------

20848-611	1	128.4 mm	Frontplatte	Front Panel without Handle	3 U	426.4 mm
20848-617	1	261.8 mm	Frontplatte	Front Panel without Handle	6 U	426.4 mm

Table 3/3

Katalognummer	Montage	Material
20848-611	Hinged, Side	Aluminium
20848-617	Hinged, Side	Aluminium

WARNUNG

nVent-Produkte müssen in Übereinstimmung mit den Produktinformationsblättern und dem Schulungsmaterial von nVent installiert und verwendet werden. Informationsblätter sind verfügbar unter www.nVent.com sowie bei Ihrem nVent-Kundendienstvertreter. Unsachgemäße Installation, Missbrauch, Fehlanwendung oder andere Handlungen im Widerspruch zu den Anweisungen und Warnungen von nVent können zu Fehlfunktionen, Anlagenschäden, schwerer Körperverletzung sowie zum Tod führen und/oder haben die Annullierung der Garantie zur Folge.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER