

TELECOM GROUNDING BUSBAR



CERTIFICATIONS



FEATURES

Meets TIA-607-C and TIA-607-D conforms to BICSI® recommendations

Complies with NEMA® standards

Accepts two hole lugs with 5/16" or 7/16" bolt holes (hardware not included)

Telecom grounding busbar splice kits are available to extend the length of the busbar

SPECIFICATIONS


Thickness (T):	6.35mm
Width (W):	50.8mm
Material:	Copper

Table 1/2						
Catalog Number	Length 1 (L1)	Length 2 (L2)	Tin Plating	Hole Size 1 Number of Pairs	Hole Size 2 Number of Pairs	с
TGBA12L06P	305mm	229mm	No	6	3	15.9mm
TGBA12L06PT	305mm	229mm	Yes	6	3	15.9mm

Catalog Number	Length 1(L1)	Length 2(L2)	Tin Plating	Hole Size 1 Number of Pairs	Hole Size 2 Number of Pairs	с
TGBA20L12PT	508mm	229mm	Yes	12	3	15.9mm
TGBA24L14P	610mm	457mm	No	14	5	15.9mm
TGBA24L14PT	610mm	457mm	Yes	14	5	15.9mm
TGBA29L18PT	737mm	457mm	Yes	18	5	15.9mm

Table 2/2					
Catalog Number	В	Α	Hole Size 1 (HS1)	Hole Size 2 (HS2)	
TGBA12L06P	28.6mm	25.4mm	8mm	11mm	
TGBA12L06PT	28.6mm	25.4mm	8mm	11mm	
TGBA20L12PT	28.6mm	25.4mm	8mm	11mm	
TGBA24L14P	28.6mm	25.4mm	8mm	11mm	
TGBA24L14PT	28.6mm	25.4mm	8mm	11mm	
TGBA29L18PT	28.6mm	25.4mm	8mm	11mm	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

▲ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.



Our powerful portfolio of brands: nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF TRACER

© 2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.

3