

19" FAN UNIT, 1 U, REMOTE CONTROL AND MONITORING

Fan Unit with ModBus interface for installation into a 1 U space within the Cabinet

FEATURES

Fan speed temperature controlled

ModBus Interface for Remote Monitoring and Control

Temperature threshold for the fan control adjustable on the front panel

Signaling of fan failure and over temperature by 2 LEDs and potential-free relay outputs

Integrated power supply with wide range input (100 V – 240 V)

Less than 1 U (42 mm) to enable mounting on sliding guide rails or drawer

2 NTC temperature sensors with Cables included

SPECIFICATIONS

Table 1/2

Catalog Number	Airflow	Noise Level	Power	Max Static Pressure	Ambient Temperature	Lifespan, L10 @ 40 C
10713-554	1089 m³/h	59.5 dB(A)	97 W	78 Pa	-10 to 70 °C	99558 h

Table 2/2

Catalog Number	Product Type	Input Voltage AC
10713-554	Fan Unit	100 – 240 V

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER