

SOCKET STRIP, IEC C19



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack with IEC C19 outlets.

CERTIFICATIONS



FEATURES

Socket strips with C19 IEC sockets

Socket strips can be rotated through all four directions (in 90° increments) during installation

Connecting cable 2 m, with connector in accordance with IEC 60309

Mounting height 1 U

SPECIFICATIONS

Table 1/2

Catalog Number	Voltage AC	Height	Product Type	Socket Type	Depth	Color
60110-280	230 V	44 mm	Socket Strip	IEC C19	44 mm	Grey
60110-281	230 V	44 mm	Socket Strip	IEC C19	44 mm	Grey
60110-282	230 V	44 mm	Socket Strip	IEC C19	44 mm	Grey

Table 2/2

Catalog Number	Length
60110-280	438.5 mm

Catalog Number	Length
60110-281	947.5 mm
60110-282	947.5 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER