


TBHS BENDABLE ROUND DUCT FIXING WITH SOUND REDUCER, V-SHAPE



FEATURES

Includes holes for pop-rivet connection

SPECIFICATIONS



Table 1/2

| Catalog Number | Article Number | Material | Finish | Hole Size 1 (HS1) | Hole Size 2 (HS2) | Hole Size 3 (HS3) |
|----------------|----------------|------------------------|-------------------|-------------------|-------------------|-------------------|
| TBHS | 597575 | Steel, EPDM-SBR Rubber | Electrogalvanized | 8.4 mm | 8.5 mm | 4.2 |

Table 2/2

| Catalog Number | Article Number | Height (H) | Width (W) | Thickness (T) | X |
|----------------|----------------|------------|-----------|---------------|-------------|
| TBHS | 597575 | 95 mm | 40 mm | 2 mm | 8.5 x 20 mm |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER