


JOINT BOND MOLD PAIR ONLY, SIGNAL, HEAD-FREE RAIL, HEAD FREE BOND
TERMINAL STYLE, MOLD ONLY, 3/16" BONDSTRAND

CATALOG NUMBER

SBS925M



FEATURES

Pair of replacement molds designed for the installation of jumper bonds to the head of the rail

Connection is made within the confines of the splice plate

PRODUCT ATTRIBUTES

Material: Graphite

Rail Type: Head-Free Rail

Bond Terminal Style: Head Free

Product: Mold only

Conductor Size: 3/16" Bondstrand

Conductor Outer Diameter, Nominal: 4.76mm

Welder Style: T6; T7

Mold Only: Yes

Welding Material: SB25, Sold Separately

Handle Clamp: C105B, Sold Separately

Conductor Sleeve: SBS11C, Sold Separately

Bond Clip: S2659, Sold Separately

Hammer Die: SBD50, Sold Separately

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER