

BASIC PDU, EB0450, 400 VAC, 3-PH, 16 A

CATALOG NUMBER

**EB0450**



Modular, compact PDU. Ultra-Low Profile Design

FEATURES

Enlogic Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage 400 VAC, 3-phase

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

PRODUCT ATTRIBUTES

Product Type: Socket Strip

Socket Type: (21) C13/C19

Socket Quantity: 42

Color: Black

Switched Outlets: No

Circuit Breaker: No Circuit Breaker

Circuit Breaker Quantity: 0

Current Rating: 11A

Finish: Powder Coated

Height: 1490mm

Input Cable Length: 1.8m

Input Cable Location: Top Feed

Input Current: 16 A / 20 A (16 A derated)

Input Voltage: 380-415 VAC, 3 PH

Max Power Input: 11.5 / 11.0 kVA

Metering Type: None

Nominal Voltage: 415V

On/Off Switch Included: No

Output Voltage: 208 – 230VAC

Package Quantity: 1

Plug Type: IEC 60309 520P6/516P6

Product Family: Enlogic

Rack Units: 0U

Removable Input Cable: No

Type: Basic PDU

## ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**