

FRONT PANEL ALTERNATIVE FOR COMBINED MOUNTING



The 2 HP wide front panel covers an open slot. The U-profile front panel can be combined with a textile EMC gasket. It be fixed with screws and washers. Due to the 2 HP width no sleeves can be used.

CERTIFICATIONS



FEATURES

U-profile front panel 6 U, 2 HP, Al, 2.5 mm

Prepared for textile EMC gasket

SPECIFICATIONS

Table 1/2

Catalog Number	Treated Edges	Front Finish	Rear Finish	Package Quantity	Product Type	Product Family
30849-140	No	Anodized	Conductive	5	Front Panel	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO

Table 2/2

Catalog Number	Works With	Rack Height
30849-140	Subracks, Cases	6 U

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER