nVent
DATA-SOLUTIONS

ELECTRICAL EARTH BAR, BARE, 4 CONNECTIONS, 0 NUMBER OF DISCONNECTS, 300 MM

CATALOG NUMBER

EEB04C506D0A



FEATURES

- Provides a convenient, single-point grounding and bonding location
- Busbars with disconnect links allow for convenient testing of the earth termination system
- High conductivity, hard drawn, electrolytic tough pitch copper per EN 13601
- Includes halogen-free polyamide insulators, stainless steel (EN 1.4401) hardware and mounting brackets
- Custom bars can be designed and manufactured to customer specifications

PRODUCT ATTRIBUTES

- Complies With: IEC® EN 62561-1:2017 Class H
- Material: Copper
- Finish: Bare
- Number of Connections: 4
- Number of Disconnects: 0
- Thread Size (TS): M10
- Height (H): 94mm
- Length (L): 300mm
- Width 1 (W1): 100mm
- Width 2 (W2): 50mm
- Thickness (T): 6mm

A: 50mm

Unit Weight: 1.45kg

ADDITIONAL PRODUCT DETAILS

Tinned finish is 8 microns according to ASTM B545 Service Class "C" for corrosive environments.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.