

19" FAN UNIT, 1 U, WITH FRONT SWITCH

Front-mounted, illuminated mains switch on AC devices, coupled with additional rear mains outlet; mechanical strain relief for mains input and mains output cables.



CERTIFICATIONS



FEATURES

Can be adapted to subracks

Contact protection in accordance with DIN EN ISO 13857

SPECIFICATIONS

Table 1/1

Catalog Number	Input Voltage DC	Product Type	Input Voltage AC	Accessory Type
10713-108		Fan Unit	230 V min	Fan unit, 19"
10713-110		Fan Unit	115 V min	Fan unit, 19"
10713-112		Fan Unit	230 V min	Fan unit, 19"
10713-114		Fan Unit	115 V min	Fan unit, 19"
10713-111	24 V min	Fan Unit		Fan unit, 19"
10713-115	24 V min	Fan Unit		Fan unit, 19"

ADDITIONAL PRODUCT DETAILS

Please order mains cable separately.

Wide-range input voltage (86 ... 264 VAC) available on request.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER