

SOCKET STRIP, IEC C13, WITH WIELAND® INPUT



Modular, compact PDU with many function elements. Using a 1 U by 1 U aluminum chassis the PDU can easily be integrated in a rack. The Wieland connector allows easy combination with different power input cords.

CERTIFICATIONS



FEATURES

Input via Wieland® GST 18 plug

Installation height 1 U

In accordance with IEC 60320

Horizontal or vertical mounting

Output via IEC 60320 C-13 sockets

Socket strips can be rotated through all four directions (in 90° increments) during fitting

SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Socket Type	Socket Quantity	Switched Outlets	Color	Voltage AC
60110-340	Socket Strip	IEC C13	12	No	Grey	230V
60110-341	Socket Strip	IEC C13	12	No	Black	230V
60110-342	Socket Strip	IEC C13	12	No	Red	230V
60110-349	Socket Strip	IEC C13	6	No	Grey	230V

Catalog Number	ProductType	Socket Type	Socket Quantity	Switched Outlets	Color	Voltage AC
60110-350	Socket Strip	IEC C13	6	No	Black	230V
60110-351	Socket Strip	IEC C13	6	No	Red	230V

Table 2/2						
Catalog Number	Function	Length	Depth	Material	Finish	Package Quantity
60110-340		438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-341		438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-342		438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-349	Overcurrent Protection	438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-350	Overcurrent Protection	438.5mm	44mm	Aluminum, Polyamide	Anodized	1
60110-351	Overcurrent Protection	438.5mm	44mm	Aluminum, Polyamide	Anodized	1

ADDITIONAL PRODUCT DETAILS

Please order mounting bracket for vertical mounting separately.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER