

C-CHANNEL 2-2 ANGLE BRACKET



FEATURES

Universally applicable for the construction of assembly systems

SPECIFICATIONS

Finish: Electrogalvanized

Material: Steel


Table 1/2

Catalog Number	Article Number	Channel Type	Angle (a)	A	B	C
EBL250A90	584666	E0, E0L, E1	90 °	25 mm	90 mm	4 mm
EBL35A090	587510	E2, E2L, E3, E4	90 °	35 mm	90 mm	4 mm

Table 2/2

Catalog Number	Article Number	D	Hole Size (HS)
EBL250A90	584666	44 mm	10.5 mm
EBL35A090	587510	44 mm	10.5 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

nVent.com **CADDY** **ERICO** **HOFFMAN** **RAYCHEM** **SCHROFF**

TRACER