


NVENT ERICO PERMAGROUND COMPRESSION CONNECTOR, C-CRIMPS



The nVent ERICO Permaground Compression Connector, C-Crimps are part of the nVent ERICO Permaground Compression Grounding Connectors line. These C-Crimps are designed to join two grounding conductors together in a grounding system using a compression tool. Made from high-strength conductive copper, they ensure a low resistance connection that eliminates corrosion, resulting in a long-lasting connection. With range-taking abilities, the C-Crimps are compatible with various conductors. To prevent oxidation, the inner surface of the C-Crimps is prefilled with an oxide inhibitor that forms an airtight seal around the conductors once the connection is completed. This makes the C-Crimp connector suitable for a wide range of applications. Additionally, the C-Crimp is marked with both metric and imperial conductor sizes and can be installed in all weather conditions.

FEATURES

- The C-Crimp's design makes it compatible with a wide range of conductors
- Dies are interchangeable with tools from nVent ILSCO TaskMaster and other manufacturers
- The C-Crimp connector is versatile, suitable for various job site applications and conductor configurations
- Quick and easy installation, with repeatable connections made in minutes
- The applied oxide inhibitor, containing flecks of copper, provides improved pull-out strength and reduces operating temperatures for copper terminations
- Installation dies leave an embossment on the finished connection for positive inspection
- Tested in accordance with UL 467 and CSA certification

SPECIFICATIONS


Table 1/2						
Catalog Number	Material	Conductor Type	Main/Run Conductor Range	Tap Conductor Range	Connection Type	Number of Crimps
ULT-1-MM	Copper	Solid, Stranded	4 - 4 mm ²	4 - 4 mm ²	Conductor to Conductor	1
ULT-2-MM	Copper	Solid, Stranded	10 - 6 mm ²	6 - 6 mm ²	Conductor to Conductor	1
ULT-3-MM	Copper	Stranded	25 - 16 mm ²	10 - 10 mm ²	Conductor to Conductor	1

Catalog Number	Material	Conductor Type	Main/Run Conductor Range	Tap Conductor Range	Connection Type	Number of Crimps
ULT-4-MM	Copper	Solid, Stranded	25 - 16 mm ²	16 - 16 mm ²	Conductor to Conductor	1
ULT-5-MM	Copper	Stranded	25 - 16 mm ²	25 - 25 mm ²	Conductor to Conductor	1
ULT-7-MM	Copper	Stranded, Stranded	35 - 35 mm ²	35 - 35 mm ²	Conductor to Conductor	2
ULT-6-MM	Copper	Stranded	35 - 35 mm ²	25 - 10 mm ²	Conductor to Conductor	2
ULT-8-MM	Copper	Stranded	70 - 50 mm ²	35 - 10 mm ²	Conductor to Conductor	3
ULT-9-MM	Copper	Solid, Stranded	70 - 50 mm ²	70 - 50 mm ²	Conductor to Conductor	1
ULT-11-MM	Copper	Stranded	120 - 95 mm ²	70 - 50 mm ²	Conductor to Conductor	1
ULT-10-MM	Copper	Solid, Stranded	95 - 95 mm ²	25 - 16 mm ²	Conductor to Conductor	1
ULT-12-MM	Copper	Stranded	95 - 95 mm ²	95 - 95 mm ²	Conductor to Conductor	1

Table 2/2

Catalog Number	Length (L)	Width (W)	Height (H)	Unit Weight	Direct Burial
ULT-1-MM	9.3 mm	7.1 mm	8.7 mm	0.002 kg	Yes
ULT-2-MM	12.3 mm	9 mm	12.7 mm	0.006 kg	Yes
ULT-3-MM	18.7 mm	11.9 mm	15.6 mm	0.015 kg	Yes
ULT-4-MM	19.4 mm	11.7 mm	17.8 mm	0.019 kg	Yes
ULT-5-MM	21.1 mm	11.9 mm	17.8 mm	0.019 kg	Yes
ULT-7-MM	26.6 mm	15.6 mm	21 mm	0.037 kg	Yes
ULT-6-MM	25.1 mm	15.6 mm	21.1 mm	0.039 kg	Yes
ULT-8-MM	34.3 mm	20.6 mm	23.5 mm	0.07 kg	Yes
ULT-9-MM	34.3 mm	20.6 mm	23.5 mm	0.07 kg	Yes
ULT-11-MM	41.4 mm	25.4 mm	27.3 mm	0.12 kg	Yes
ULT-10-MM	41.4 mm	25.4 mm	27.3 mm	0.14 kg	Yes
ULT-12-MM	40.9 mm	25.4 mm	30.5 mm	0.14 kg	Yes

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER