

## RACKPOWER SINGLE TEMPERATURE AND HUMIDITY SENSOR

Single Temperature and Humidity Probe Sensor for nVent  
SCHROFF RackPower PDU's.

### FEATURES

Single Temperature and Humidity Sensor

With 2 Meter cable and integrated magnet for easy mounting

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Temperature Measuring Range 0 to 65 °C

Temperature Measuring Accuracy +- 2 %

Humidity Measuring Range 10-90% RH, Non-Condensing

Humidity Measuring Accuracy +- 5 %

### SPECIFICATIONS

Table 1/1

Catalog Number	Product Type	Works With	Type
EA9103	Sensor	RackPower	Temperature and Humidity

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**