



## NVENT CADDY SPEED LINK SLK WITH TOGGLE



### CERTIFICATIONS



### FEATURES

Complete system includes wire, locking device and pre-assembled toggle end fitting

Attaches to clearance holes in a variety of structures or hanging devices

Ideal for supporting lighting fixtures

Also available in Y-toggle configuration

### SPECIFICATIONS

<b>Wire Rope Diameter:</b>	1.5 mm
<b>Static Load Safety Factor:</b>	5:1
<b>Finish:</b>	Electrogalvanized
<b>Material:</b>	Steel;Zinc Alloy;Polypropylene
<b>Complies With:</b>	SMACNA HVAC-DCS

Table 1/1

Catalog Number	Article Number	Wire Rope Length	A	B	Static Load (F)	Packing Quantity
SLK15L10T	196526	10m	39 mm	5 mm	195N	1.0000

Catalog Number	Article Number	Wire Rope Length	A	B	Static Load (F)	Packing Quantity
SLK15L1T	196521	1m	39 mm	5 mm	195N	1.0000
SLK15L2T	196522	2m	39 mm	5 mm	195N	1.0000
SLK15L2TR2	196644	2m	39 mm	5 mm	195N	2.0000
SLK15L3T	196523	3m	39 mm	5 mm	195N	1.0000
SLK15L5T	196524	5m	39 mm	5 mm	195N	1.0000
SLK15L7T	196525	7m	39 mm	5 mm	195N	1.0000


**Thickness (T):** 12.5 mm

**Width (W):** 19 mm

**Height (H):** 55 mm

**Angle (a):** 90 ° Max

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**