

## RACKPOWER SINGLE TEMPERATURE SENSOR



Single Temperature Probe Sensor for nVent SCHROFF  
RackPower PDU's.

### FEATURES

Single Temperature Sensor

With 2 Meter cable and integrated magnet for easy mounting

For RackPower RP1xxx, RP2xxx, RP6xxx Series PDU's

Hot pluggable for easy integration

Temperature Measuring Range 0 to 65 °C

Temperature Measuring Accuracy +/- 2 %

### SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Product Family	Works With	Package Quantity	Height	Removable Input Cable
EA9102	Sensor	Enlogic	RackPower	1	270mm	No

Table 2/2

Catalog Number	Plug Type
EA9102	RJ45

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**