

## FRONT PANEL, FRONT SHIELDED, SIDE HINGED

Front panel with textile EMC gasket, side hinged assembly.



### CERTIFICATIONS



### FEATURES

Front panel with textile EMC gasket

Enables mounting onto the horizontal rails

Suitable for subracks and cases

Hinges can be fitted on left or right

### SPECIFICATIONS

Table 1/3

Catalog Number	EMC Gasket Type	Treated Edges	Front Finish	Rear Finish	EMC Shielding	Rack Width
20848-611	Textile	No	Anodized	Conductive	No (Retrofittable)	84 HP
20848-617	Textile	No	Anodized	Conductive	No (Retrofittable)	84 HP

Table 2/3

Catalog Number	Package Quantity	Height	Product Type	Type	Rack Height	Width
----------------	------------------	--------	--------------	------	-------------	-------

20848-611	1	128.4 mm	Front Panel	Front Panel without Handle	3 U	426.4 mm
20848-617	1	261.8 mm	Front Panel	Front Panel without Handle	6 U	426.4 mm

Table 3/3

Catalog Number	Mounting	Material
20848-611	Hinged, Side	Aluminum
20848-617	Hinged, Side	Aluminum

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**