



NVENT CADDY SPEED LINK CATENARY LOCKING DEVICE



FEATURES

- Push/pull keyless release allows easy adjustments
- Low-profile locking device minimizes visual impact
- Cable spread of 60 degrees allows positioning the device closer to the structure
- Keyless release tubes are easy to operate while wearing gloves


SPECIFICATIONS

Table 1/1						
Catalog Number	Article Number	Material	Wire Rope Diameter	Height (H)	Width (W)	Thickness (T)
SLK6C2	196820	Steel, Polypropylene, Zinc Alloy	6 mm	108 mm	41 mm	30 mm

ADDITIONAL PRODUCT DETAILS

Locking devices are only to be used with nVent CADDY Speed Link wire spools and accessories with the same specified Wire Rope Diameter as the locking device. Do not use with any other wires.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

nVent.com **CADDY** **ERICO** **HOFFMAN** **RAYCHEM** **SCHROFF**

TRACER