

OPEN FRAME RACK 2-POST



Designed for use in communication data centers and telecommunication rooms, 2-Post Open Frame Racks satisfy basic functional requirements for structuring cable. Racks are available in 3-inch or 6-inch column widths.

INDUSTRY STANDARDS

UL 2416 Listed; File No. E230874

cUL Listed per CSA C22.2 No. 182.4; File No. E230874

EIA 310-D

FEATURES

Range of heights from 4 feet to 9 feet (24U to 58U) to match capacity requirements; 19-inch Rack Packages are 7-feet high

Side rails are tapped on both sides with 12-24UNC threads for quick installation

EIA Universal 5/8 inch - 5/8 inch - 1/2 inch vertical mounting hole pattern matches industry standards

RU markings on both front and back of uprights make it easier to mount equipment

Packed unassembled in individual cartons; assembly hardware is furnished for convenient storage and installation

Convenient rack and cable manager packages offered with either one or two 6-inch cable managers; includes one-piece hinged cover

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Rack Units	Height	Finish	Material	Color
EDR19FM24U	21599	24U	1219mm	Powder Coated	Aluminum	Jet Black
EDR19FM38U	21609	38U	1829mm	Powder Coated	Aluminum	Jet Black
EDR19FM45U	21619	45U	2134mm	Powder Coated	Aluminum	Jet Black
EDR19FM45U6	25324	45U	2134mm	Powder Coated	Aluminum	Jet Black
EDR19FM45UC M1	14643	45U	2134mm	Powder Coated	Aluminum	Jet Black
EDR19FM45UC M2	14644	45U	2134mm	Powder Coated	Aluminum	Jet Black
EDR19FM51U	21629	51U	2438mm	Powder Coated	Aluminum	Jet Black
EDR19FM51U6	25325	51U	2438mm	Powder Coated	Aluminum	Jet Black

Catalog Number	Article Number	Rack Units	Height	Finish	Material	Color
EDR19FM58U	35309	58U	2743mm	Powder Coated	Aluminum	Jet Black
EDR23FM24U	21649	24U	1219mm	Powder Coated	Aluminum	Jet Black
EDR23FM38U	21659	38U	1829mm	Powder Coated	Aluminum	Jet Black
EDR23FM45U	21669	45U	2134mm	Powder Coated	Aluminum	Jet Black
EDR23FM51U	21679	51U	2438mm	Powder Coated	Aluminum	Jet Black
EVR19FM45U	22019	45U	2134mm	Mill	Aluminum	
EVR19FM51U	22029	51U	2438mm	Mill	Aluminum	
EVR19FM58U	35319	58U	2743mm	Mill	Aluminum	
EVR23FM45U	22039	45U	2134mm	Mill	Aluminum	
EVR23FM51U	22049	51U	2438mm	Mill	Aluminum	
EWR19FM45U	36108	45U	2134mm	Mill	Aluminum	White

Table 2/2					
Catalog Number	Article Number	Color Code	Width	Depth	Thickness
EDR19FM24U	21599	RAL 9005	514mm	381mm	3.5mm
EDR19FM38U	21609	RAL 9005	514mm	381mm	3.5mm
EDR19FM45U	21619	RAL 9005	514mm	381mm	3.5mm
EDR19FM45U6	25324	RAL 9005	515mm	457mm	3.5mm
EDR19FM45UCM1	14643	RAL 9005	699mm	457mm	3.5mm
EDR19FM45UCM2	14644	RAL 9005	883mm	457mm	3.5mm
EDR19FM51U	21629	RAL 9005	514mm	381mm	3.5mm
EDR19FM51U6	25325	RAL 9005	515mm	457mm	3.5mm
EDR19FM58U	35309	RAL 9005	514mm	381mm	3.5mm
EDR23FM24U	21649	RAL 9005	616mm	381mm	3.5mm
EDR23FM38U	21659	RAL 9005	616mm	381mm	3.5mm
EDR23FM45U	21669	RAL 9005	616mm	381mm	3.5mm
EDR23FM51U	21679	RAL 9005	616mm	381mm	3.5mm
EVR19FM45U	22019		514mm	381mm	3.5mm
EVR19FM51U	22029		514mm	381mm	3.5mm
EVR19FM58U	35319		514mm	381mm	3.5mm
EVR23FM45U	22039		616mm	381mm	3.5mm
EVR23FM51U	22049		616mm	381mm	3.5mm
EWR19FM45U	36108	RAL 9003	514mm	381mm	3.5mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER