



# NVENT CADDY SPEED LINK SLK WITH Y-TOGGLE



## CERTIFICATIONS



## FEATURES

- Complete system includes wire, locking device and two pre-assembled toggle end fittings
- Attaches to clearance holes in a variety of structures or hanging devices
- Ideal for supporting lighting fixtures

## SPECIFICATIONS

<b>Wire Rope Diameter:</b>	1.5 mm
<b>Static Load Safety Factor:</b>	5:1
<b>Finish:</b>	Electrogalvanized
<b>Material:</b>	Steel;Zinc Alloy;Polypropylene
<b>Complies With:</b>	SMACNA HVAC-DCS

Table 1/2						
Catalog Number	Article Number	Wire Rope Length	Wire Rope "Y" Length (YL)	A	B	Static Load (F)
SLK15Y300L3R 2	196648	3m	0.3m	39 mm	5 mm	195N

Catalog Number	Article Number	Wire Rope Length	Wire Rope "Y" Length (YL)	A	B	Static Load (F)
SLK15Y500L3	196528	3m	0.5m	39 mm	5 mm	195N

Table 2/2

Catalog Number	Article Number	Packing Quantity
SLK15Y300L3R2	196648	2.0000
SLK15Y500L3	196528	1.0000




**Thickness (T):** 12.5 mm

**Width (W):** 19 mm

**Height (H):** 55 mm

**Angle (a):** 90 ° Max

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical Support

#### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

#### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

#### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**