

## THREADED STUD



### FEATURES

Pre-cut lengths of threaded rod

### SPECIFICATIONS


**Quality Class:** 4.6  
**Finish:** Electrogalvanized  
**Material:** Steel

Table 1/1

Catalog Number	Article Number	Rod Size (RS)	Length (L)
051M10025	400345	M10	25 mm
051M8025	400336	M8	25 mm
051M10040	400346	M10	40 mm
051M8040	400337	M8	40 mm
051M10060	400347	M10	60 mm
051M8060	400338	M8	60 mm
051M8070	593465	M8	70 mm
051M10080	400349	M10	80 mm
051M8080	400340	M8	80 mm
051M10090	593505	M10	90 mm
051M10100	400351	M10	100 mm
051M8100	400342	M8	100 mm

Catalog Number	Article Number	Rod Size (RS)	Length (L)
051M10150	593516	M10	150 mm
051M8120	593476	M8	120 mm
051M8150	593477	M8	150 mm

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

<b>North America</b> +1.800.753.9221 Option 1 – Customer Care Option 2 – Technical Support	<b>Europe</b> Netherlands: +31 800-0200135 France: +33 800 901 793	<b>Europe</b> Germany: 800 1890272 Other Countries: +31 13 5835404	<b>APAC</b> Shanghai: + 86 21 2412 1618/19 Sydney: +61 2 9751 8500
---	--	--	--