



# STRUT NUT WITHOUT SPRING



## FEATURES

Used to create metal frames with nVent CADDY Eristrut channels

## SPECIFICATIONS

**Static Load Safety Factor:** 3:1


Table 1/1

| Catalog Number | Article Number | Material                        | Finish             | Rod Size (RS) | Thickness (T) | Torque (TQ) |
|----------------|----------------|---------------------------------|--------------------|---------------|---------------|-------------|
| NUTM6EG        | 314995         | Steel                           | Electrogalvanized  | 6             | 6 mm          | 12 N·m      |
| NUTM6HD        | 315000         | Steel                           | Hot-Dip Galvanized | 6             | 6 mm          | 12 N·m      |
| NUTM6S6        | 315140         | Stainless Steel 316 (EN 1.4401) |                    | 6             | 6 mm          | 12 N·m      |
| NUTM8EG        | 315015         | Steel                           | Electrogalvanized  | 8             | 6 mm          | 28 N·m      |
| NUTM8HD        | 315010         | Steel                           | Hot-Dip Galvanized | 8             | 6 mm          | 28 N·m      |
| NUTM8S6        | 315150         | Stainless Steel 316 (EN 1.4401) |                    | 8             | 6 mm          | 28 N·m      |
| NUTM10EG       | 315025         | Steel                           | Electrogalvanized  | 10            | 8 mm          | 55 N·m      |

| Catalog Number | Article Number | Material                        | Finish             | Rod Size(RS) | Thickness(T) | Torque (TQ) |
|----------------|----------------|---------------------------------|--------------------|--------------|--------------|-------------|
| NUTM10HD       | 315020         | Steel                           | Hot-Dip Galvanized | 10           | 8 mm         | 55 N·m      |
| NUTM10S6       | 315160         | Stainless Steel 316 (EN 1.4401) |                    | 10           | 8 mm         | 55 N·m      |
| NUTM12EG       | 315035         | Steel                           | Electrogalvanized  | 12           | 8 mm         | 55 N·m      |
| NUTM12HD       | 315030         | Steel                           | Hot-Dip Galvanized | 12           | 8 mm         | 55 N·m      |
| NUTM12S6       | 315170         | Stainless Steel 316 (EN 1.4401) |                    | 12           | 8 mm         | 55 N·m      |
| NUTM16EG       | 315036         | Steel                           | Electrogalvanized  | 16           | 11.7 mm      | 125 N·m     |
| NUTM16HD       | 315037         | Steel                           | Hot-Dip Galvanized | 16           | 11.7 mm      | 125 N·m     |

| Pull-Out Strength |              |                   |        |        |
|-------------------|--------------|-------------------|--------|--------|
| Part Number       | Channel Type | Channel Thickness |        |        |
|                   |              | 2,5 mm            | 2 mm   | 1,5 mm |
| NUTM6xx           | A, C         | 2000 N            | 2000 N | 2000 N |
|                   | D, E         | 2000 N            | -      | -      |
| NUTM8xx           | A, C         | 3330 N            | 3330 N | 3330 N |
|                   | D, E         | 3330 N            | -      | -      |
| NUTM10xx          | A, C         | 4890 N            | 4440 N | 4440 N |
|                   | D, E         | 4890 N            | -      | -      |
| NUTM12xx          | A, C         | 4890 N            | 4660 N | 4440 N |
|                   | D, E         | 3670 N            | -      | -      |
| NUTM12Txx         | A            | 5670 N            | 5050 N | 4440 N |
|                   | D, E         | 4250 N            | -      | -      |
| NUTM16xx          | A            | 5670 N            | 4660 N | 4440 N |
|                   | D, E         | 4250 N            | -      | -      |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**