

MONITOR, KEYBOARD, TOUCHPAD, 1 U DRAWER, REDUCED DEPTH



Designed for standard 19" rackmount designed for comfort
robust design for heavy use or harsh environment operation

CERTIFICATIONS



FEATURES

Pull-out 17" TFT color monitor chassis, 1 U (resolution Full HD; connects to VGA or DVI-D interface)

Keyboard with different keyboard layout (connects via USB)

Integral touchpad (connects via USB)

Voltage supply: Wide-range input (nominal mains voltage 110 to 240 VAC), Voltage supply 12, 24 and 48 VDC on request

Depth-adjustable mounting for different pitches of server panel/slide mounts; Mounting depth (dimension c = spacing of 19" profiles): dimension c 450 ... 640 mm

With DVI connection

SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Type	Works With	Color	Color Code	Rack Height
60118-583	Cabinet/Rack Drawer	Monitor, Keyboard, Touchpad	19" Cabinets	Jet Black	RAL 9005	1U

Catalog Number	ProductType	Type	Works With	Color	Color Code	Rack Height
60118-584	Cabinet/Rack Drawer	Monitor, Keyboard, Touchpad	19" Cabinets	Jet Black	RAL 9005	1U

Table 2/2

Catalog Number	Depth
60118-583	400mm
60118-584	400mm

ADDITIONAL PRODUCT DETAILS

Further versions on request – With trackball or numeric pad.

Other Keyboard layouts see user manual.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER