

SECURE DUAL W-LOCK POWER CORD



Secure dual W-Lock power cords provide enhanced cord retention between both the PDU and IT equipment. Both connections require deliberate action in order to release the locking buttons to prevent accidental detachment of power connections. Cords function with any corresponding standard IEC receptacle, but locking feature requires compatible W-lock or V-lock outlets

FEATURES

Secure dual locking power cords

The IEC C14/C20 plug will lock into any RackPower PDU

The universal locking IEC connector will securely lock into any standard C14/C20 power inlet

Both connections require deliberate action in order to release the locking buttons and disconnect power

SPECIFICATIONS

Table 1/2

Catalog Number	Product Type	Product Family	Type	Works With	Length	Color
EP1314024X150	Cable	Enlogic	Cable	RackPower	600mm	Black
EP1314048X125	Cable	Enlogic	Cable	RackPower	1200mm	Black
EP1314072X100	Cable	Enlogic	Cable	RackPower	1800mm	Black
EP1314B24X150	Cable	Enlogic	Cable	RackPower	600mm	Blue
EP1314B48X125	Cable	Enlogic	Cable	RackPower	1200mm	Blue
EP1314B72X100	Cable	Enlogic	Cable	RackPower	1800mm	Blue
EP1314R24X150	Cable	Enlogic	Cable	RackPower	600mm	Red
EP1314R48X125	Cable	Enlogic	Cable	RackPower	1200mm	Red
EP1314R72X100	Cable	Enlogic	Cable	RackPower	1800mm	Red
EP1920024X100	Cable	Enlogic	Cable	RackPower	600mm	Black

Catalog Number	ProductType	Product Family	Type	Works With	Length	Color
EP1920048X75	Cable	Enlogic	Cable	RackPower	1200mm	Black
EP1920072X50	Cable	Enlogic	Cable	RackPower	1800mm	Black
EP1920B24X100	Cable	Enlogic	Cable	RackPower	600mm	Blue
EP1920B48X75	Cable	Enlogic	Cable	RackPower	1200mm	Blue
EP1920B72X50	Cable	Enlogic	Cable	RackPower	1800mm	Blue
EP1920R24X100	Cable	Enlogic	Cable	RackPower	600mm	Red
EP1920R48X75	Cable	Enlogic	Cable	RackPower	1200mm	Red
EP1920R72X50	Cable	Enlogic	Cable	RackPower	1800mm	Red

Table 2/2

Catalog Number	Height	Package Quantity	Plug Type	Input Cable Length	Removable Input Cable
EP1314024X150	270mm	150	C13/C14	588m	No
EP1314048X125	270mm	125	C13/C14	1.176m	No
EP1314072X100	270mm	100	C13/C14	1.764m	No
EP1314B24X150	270mm	150	C13/C14	0.588m	No
EP1314B48X125	270mm	125	C13/C14	1.176m	No
EP1314B72X100	270mm	100	C13/C14	1.764m	No
EP1314R24X150	270mm	150	C13/C14	0.588m	No
EP1314R48X125	270mm	125	C13/C14	1.176m	No
EP1314R72X100	270mm	100	C13/C14	1.764m	No
EP1920024X100	270mm	100	C19/C20	0.588m	No
EP1920048X75	270mm	75	C19/C20	1.176m	No
EP1920072X50	270mm	50	C19/C20	1.764m	No
EP1920B24X100	270mm	100	C19/C20	0.588m	No
EP1920B48X75	270mm	75	C19/C20	1.176m	No
EP1920B72X50	270mm	50	C19/C20	1.764m	No
EP1920R24X100	270mm	100	C19/C20	0.588m	No
EP1920R48X75	270mm	75	C19/C20	1.176m	No
EP1920R72X50	270mm	50	C19/C20	1.764m	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction,

property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER