

CRIMPING COMPRESSION TOOL, MANUAL

CATALOG NUMBER

M2M



FEATURES

Wide cross section range
Ergonomic design
Lightweight and easy to use
Includes easy-to-carry custom case

PRODUCT ATTRIBUTES

Article Number: 716900
System: Manual
Dies: RKM2 series; PKM2 series
Crimping Shape: Hexagon
Conductor Size: #10 Stranded - 600 kcmil Stranded; 6 mm² Stranded - 300 mm² Stranded

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER