

## SWITCHED PDU OUTLET AND ENVIRONMENTAL MONITOR, FITS 19IN RACK, BLACK, STEEL

### CATALOG NUMBER

**DPC1N119820**



The Switched PDU Outlet and Environmental Monitor provides power, switched outlet and environmental monitoring for quick access to current, volts, power and kilowatt hours. It allows users to remotely disable specific outlets to neutralize or reboot problem equipment avoiding downtime.

### FEATURES

Local LCD display, includes port for optional remote display

Provides environmental monitoring with two RJ12 ports for plug-and-play optional sensors (ordered separately)

Ethernet connectivity

19-in. rack-mount horizontal model has 15A, 120V, (8) NEMA 5-15R outlets

10-ft. power cord with 5-15P

### PRODUCT ATTRIBUTES

Article Number: 17311

Width: 432mm

Material: Mild Steel

Finish: Powder Coated

Color: Jet Black

Thickness: 1.52mm

Type: Control PDU, 19-in. Rack-Mount

Voltage AC: 120V

Electrical Load Rating: 20A

Depth: 216mm

Receptacle Quantity: 8

Receptacle Style: 5-15R

Color Code: RAL 9005

## **WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**

© 2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.