

## SECURE DUAL W-LOCK POWER CORD



Secure dual W-Lock power cords provide enhanced cord retention between both the PDU and IT equipment. Both connections require deliberate action in order to release the locking buttons to prevent accidental detachment of power connections. Cords function with any corresponding standard IEC receptacle, but locking feature requires compatible W-lock or V-lock outlets

### FEATURES

Secure dual locking power cords

The IEC C14/C20 plug will lock into any RackPower PDU

The universal locking IEC connector will securely lock into any standard C14/C20 power inlet

Both connections require deliberate action in order to release the locking buttons and disconnect power

### SPECIFICATIONS

Table 1/2

| Catalog Number | Product Type | Product Family | Works With | Length | Type  | Package Quantity |
|----------------|--------------|----------------|------------|--------|-------|------------------|
| EP1314024X150  | Cable        | Enlogic        | RackPower  | 600mm  | Cable | 150              |
| EP1314048X125  | Cable        | Enlogic        | RackPower  | 1200mm | Cable | 125              |
| EP1314072X100  | Cable        | Enlogic        | RackPower  | 1800mm | Cable | 100              |
| EP1314B24X150  | Cable        | Enlogic        | RackPower  | 600mm  | Cable | 150              |
| EP1314B48X125  | Cable        | Enlogic        | RackPower  | 1200mm | Cable | 125              |
| EP1314B72X100  | Cable        | Enlogic        | RackPower  | 1800mm | Cable | 100              |
| EP1314R24X150  | Cable        | Enlogic        | RackPower  | 600mm  | Cable | 150              |
| EP1314R48X125  | Cable        | Enlogic        | RackPower  | 1200mm | Cable | 125              |
| EP1314R72X100  | Cable        | Enlogic        | RackPower  | 1800mm | Cable | 100              |
| EP1920024X100  | Cable        | Enlogic        | RackPower  | 600mm  | Cable | 100              |

| Catalog Number | ProductType | Product Family | Works With | Length | Type  | Package Quantity |
|----------------|-------------|----------------|------------|--------|-------|------------------|
| EP1920048X75   | Cable       | Enlogic        | RackPower  | 1200mm | Cable | 75               |
| EP1920072X50   | Cable       | Enlogic        | RackPower  | 1800mm | Cable | 50               |
| EP1920B24X100  | Cable       | Enlogic        | RackPower  | 600mm  | Cable | 100              |
| EP1920B48X75   | Cable       | Enlogic        | RackPower  | 1200mm | Cable | 75               |
| EP1920B72X50   | Cable       | Enlogic        | RackPower  | 1800mm | Cable | 50               |
| EP1920R24X100  | Cable       | Enlogic        | RackPower  | 600mm  | Cable | 100              |
| EP1920R48X75   | Cable       | Enlogic        | RackPower  | 1200mm | Cable | 75               |
| EP1920R72X50   | Cable       | Enlogic        | RackPower  | 1800mm | Cable | 50               |

Table 2/2

| Catalog Number | Color | Height | Removable Input Cable | Plug Type | Input Cable Length |
|----------------|-------|--------|-----------------------|-----------|--------------------|
| EP1314024X150  | Black | 270mm  | No                    | C13/C14   | 588m               |
| EP1314048X125  | Black | 270mm  | No                    | C13/C14   | 1.176m             |
| EP1314072X100  | Black | 270mm  | No                    | C13/C14   | 1.764m             |
| EP1314B24X150  | Blue  | 270mm  | No                    | C13/C14   | 0.588m             |
| EP1314B48X125  | Blue  | 270mm  | No                    | C13/C14   | 1.176m             |
| EP1314B72X100  | Blue  | 270mm  | No                    | C13/C14   | 1.764m             |
| EP1314R24X150  | Red   | 270mm  | No                    | C13/C14   | 0.588m             |
| EP1314R48X125  | Red   | 270mm  | No                    | C13/C14   | 1.176m             |
| EP1314R72X100  | Red   | 270mm  | No                    | C13/C14   | 1.764m             |
| EP1920024X100  | Black | 270mm  | No                    | C19/C20   | 0.588m             |
| EP1920048X75   | Black | 270mm  | No                    | C19/C20   | 1.176m             |
| EP1920072X50   | Black | 270mm  | No                    | C19/C20   | 1.764m             |
| EP1920B24X100  | Blue  | 270mm  | No                    | C19/C20   | 0.588m             |
| EP1920B48X75   | Blue  | 270mm  | No                    | C19/C20   | 1.176m             |
| EP1920B72X50   | Blue  | 270mm  | No                    | C19/C20   | 1.764m             |
| EP1920R24X100  | Red   | 270mm  | No                    | C19/C20   | 0.588m             |
| EP1920R48X75   | Red   | 270mm  | No                    | C19/C20   | 1.176m             |
| EP1920R72X50   | Red   | 270mm  | No                    | C19/C20   | 1.764m             |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction,

property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**

© 2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.