

VARISTAR CP FRAME

Varistar welded steel frame for static load requirements. For 19", ETSI or mounting plate integration.

FEATURES

Welded, finish powder-coated, black gray, RAL 7021

St, 1.5 mm, zinc-plated, with central GND/grounding point

Static load-carrying capacity max. 1600 kg

Please order adjustable feet separately

SPECIFICATIONS

Table 1/3

Catalog Number	Frame Material	Height	Product Type	Product Family	Works With	Type
20630-065	Steel	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-066	Steel	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-067	Steel	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-068	Steel	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-071	Steel	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-072	Steel	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-073	Steel	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-074	Steel	1200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-075	Steel	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-076	Steel	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard

Catalog Number	Frame Material	Height	ProductType	Product Family	Works With	Type
20630-077	Steel	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-078	Steel	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-079	Steel	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-080	Steel	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-081	Steel	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-082	Steel	1400 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-083	Steel	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-084	Steel	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-085	Steel	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-086	Steel	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-087	Steel	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-088	Steel	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-089	Steel	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-090	Steel	1600 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-091	Steel	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-092	Steel	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-093	Steel	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-094	Steel	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-095	Steel	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-096	Steel	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard

Catalog Number	Frame Material	Height	ProductType	Product Family	Works With	Type
20630-097	Steel	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-098	Steel	1800 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-099	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-100	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-101	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-102	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-103	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-104	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-105	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-106	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-107	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-108	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-109	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-110	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-261	Steel	2000 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-111	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-112	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-113	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-114	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-115	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard

Catalog Number	Frame Material	Height	ProductType	Product Family	Works With	Type
20630-116	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-117	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-118	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-119	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-120	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-121	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-122	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-262	Steel	2200 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-123	Steel	2450 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-124	Steel	2450 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-125	Steel	2450 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-126	Steel	2450 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-127	Steel	2450 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard
20630-128	Steel	2450 mm	Cabinet/Rack Frame	Varistar CP	Varistar CP	Standard

Table 2/3						
Catalog Number	Rack Height	Width	Complies With	Depth	Color	Material
20630-065	24 U	600 mm		600 mm	Black Grey	Steel
20630-066	24 U	600 mm		800 mm	Black Grey	Steel
20630-067	24 U	600 mm		900 mm	Black Grey	Steel
20630-068	24 U	600 mm		1000 mm	Black Grey	Steel
20630-071	24 U	800 mm		600 mm	Black Grey	Steel
20630-072	24 U	800 mm		800 mm	Black Grey	Steel
20630-073	24 U	800 mm		900 mm	Black Grey	Steel
20630-074	24 U	800 mm		1000 mm	Black Grey	Steel

Catalog Number	Rack Height	Width	Complies With	Depth	Color	Material
20630-075	29 U	600 mm		600 mm	Black Grey	Steel
20630-076	29 U	600 mm		800 mm	Black Grey	Steel
20630-077	29 U	600 mm		900 mm	Black Grey	Steel
20630-078	29 U	600 mm		1000 mm	Black Grey	Steel
20630-079	29 U	800 mm		600 mm	Black Grey	Steel
20630-080	29 U	800 mm		800 mm	Black Grey	Steel
20630-081	29 U	800 mm		900 mm	Black Grey	Steel
20630-082	29 U	800 mm		1000 mm	Black Grey	Steel
20630-083	33 U	600 mm		600 mm	Black Grey	Steel
20630-084	33 U	600 mm		800 mm	Black Grey	Steel
20630-085	33 U	600 mm		900 mm	Black Grey	Steel
20630-086	33 U	600 mm		1000 mm	Black Grey	Steel
20630-087	33 U	800 mm		600 mm	Black Grey	Steel
20630-088	33 U	800 mm		800 mm	Black Grey	Steel
20630-089	33 U	800 mm		900 mm	Black Grey	Steel
20630-090	33 U	800 mm		1000 mm	Black Grey	Steel
20630-091	38 U	600 mm		600 mm	Black Grey	Steel
20630-092	38 U	600 mm		800 mm	Black Grey	Steel
20630-093	38 U	600 mm		900 mm	Black Grey	Steel
20630-094	38 U	600 mm		1000 mm	Black Grey	Steel
20630-095	38 U	800 mm		600 mm	Black Grey	Steel
20630-096	38 U	800 mm		800 mm	Black Grey	Steel
20630-097	38 U	800 mm		900 mm	Black Grey	Steel
20630-098	38 U	800 mm		1000 mm	Black Grey	Steel
20630-099	42 U	600 mm		600 mm	Black Grey	Steel
20630-100	42 U	600 mm		800 mm	Black Grey	Steel
20630-101	42 U	600 mm		900 mm	Black Grey	Steel
20630-102	42 U	600 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel
20630-103	42 U	600 mm	IEC 61587-1, IEC 61587-3	1100 mm	Black Grey	Steel
20630-104	42 U	600 mm	IEC 61587-1, IEC 61587-3	1200 mm	Black Grey	Steel
20630-105	42 U	800 mm		600 mm	Black Grey	Steel
20630-106	42 U	800 mm		800 mm	Black Grey	Steel

Catalog Number	Rack Height	Width	Complies With	Depth	Color	Material
20630-107	42 U	800 mm		900 mm	Black Grey	Steel
20630-108	42 U	800 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel
20630-109	42 U	800 mm	IEC 61587-1, IEC 61587-3	1100 mm	Black Grey	Steel
20630-110	42 U	800 mm	IEC 61587-1, IEC 61587-3	1200 mm	Black Grey	Steel
20630-261	42 U	600 mm		300 mm	Black Grey	Steel
20630-111	47 U	600 mm		600 mm	Black Grey	Steel
20630-112	47 U	600 mm		800 mm	Black Grey	Steel
20630-113	47 U	600 mm		900 mm	Black Grey	Steel
20630-114	47 U	600 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel
20630-115	47 U	600 mm	IEC 61587-1, IEC 61587-3	1100 mm	Black Grey	Steel
20630-116	47 U	600 mm	IEC 61587-1, IEC 61587-3	1200 mm	Black Grey	Steel
20630-117	47 U	800 mm		600 mm	Black Grey	Steel
20630-118	47 U	800 mm		800 mm	Black Grey	Steel
20630-119	47 U	800 mm		900 mm	Black Grey	Steel
20630-120	47 U	800 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel
20630-121	47 U	800 mm	IEC 61587-1, IEC 61587-3	1100 mm	Black Grey	Steel
20630-122	47 U	800 mm	IEC 61587-1, IEC 61587-3	1200 mm	Black Grey	Steel
20630-262	47 U	600 mm		300 mm	Black Grey	Steel
20630-123	52 U	600 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel
20630-124	52 U	600 mm	IEC 61587-1, IEC 61587-3	1100 mm	Black Grey	Steel
20630-125	52 U	600 mm	IEC 61587-1, IEC 61587-3	1200 mm	Black Grey	Steel
20630-126	52 U	800 mm	IEC 61587-1, IEC 61587-3	1000 mm	Black Grey	Steel
20630-127	52 U	800 mm	IEC 61587-1, IEC 61587-3	1100 mm	Black Grey	Steel
20630-128	52 U	800 mm	IEC 61587-1, IEC 61587-3	1200 mm	Black Grey	Steel

Table 3/3

Catalog Number	Color Code	Static Load
20630-065	RAL 7021	
20630-066	RAL 7021	
20630-067	RAL 7021	
20630-068	RAL 7021	
20630-071	RAL 7021	
20630-072	RAL 7021	
20630-073	RAL 7021	
20630-074	RAL 7021	
20630-075	RAL 7021	
20630-076	RAL 7021	
20630-077	RAL 7021	
20630-078	RAL 7021	
20630-079	RAL 7021	
20630-080	RAL 7021	
20630-081	RAL 7021	
20630-082	RAL 7021	
20630-083	RAL 7021	
20630-084	RAL 7021	
20630-085	RAL 7021	
20630-086	RAL 7021	
20630-087	RAL 7021	
20630-088	RAL 7021	
20630-089	RAL 7021	
20630-090	RAL 7021	
20630-091	RAL 7021	
20630-092	RAL 7021	
20630-093	RAL 7021	
20630-094	RAL 7021	
20630-095	RAL 7021	
20630-096	RAL 7021	
20630-097	RAL 7021	
20630-098	RAL 7021	
20630-099	RAL 7021	
20630-100	RAL 7021	

Catalog Number	Color Code	Static Load
20630-101	RAL 7021	
20630-102	RAL 7021	1600 kgf
20630-103	RAL 7021	1600 kgf
20630-104	RAL 7021	1600 kgf
20630-105	RAL 7021	
20630-106	RAL 7021	
20630-107	RAL 7021	
20630-108	RAL 7021	1600 kgf
20630-109	RAL 7021	1600 kgf
20630-110	RAL 7021	1600 kgf
20630-261	RAL 7021	
20630-111	RAL 7021	
20630-112	RAL 7021	
20630-113	RAL 7021	
20630-114	RAL 7021	1600 kgf
20630-115	RAL 7021	1600 kgf
20630-116	RAL 7021	1600 kgf
20630-117	RAL 7021	
20630-118	RAL 7021	
20630-119	RAL 7021	
20630-120	RAL 7021	1600 kgf
20630-121	RAL 7021	1600 kgf
20630-122	RAL 7021	1600 kgf
20630-262	RAL 7021	
20630-123	RAL 7021	1600 kgf
20630-124	RAL 7021	1600 kgf
20630-125	RAL 7021	1600 kgf
20630-126	RAL 7021	1600 kgf
20630-127	RAL 7021	1600 kgf
20630-128	RAL 7021	1600 kgf

ADDITIONAL PRODUCT DETAILS

A combination of castors and castors with adjustable feet is not possible with the standard frame. Please order the mobile frame for this requirement

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER