

FRONT PANEL, SHIELDED, BOTTOM HINGED

U-profile front panel bottom hinged for textile gasket.



CERTIFICATIONS



FEATURES

U-profile front panel can be unhinged at 135° (not RatiopacPRO) opening angle

Enables mounting on horizontal rails

Shielded, U front panel with textile EMC gasket

Suitable for sub racks (EuropacPRO) and cases (RatiopacPRO, PropacPRO, CompacPRO)

SPECIFICATIONS

Accessory Type: Front panel

Table 1/3

Catalog Number	Type	Mounting	EMC Shielding	EMC Gasket Type	Material	Front Finish
20848-608	Front Panel without Handle	Hinged, Bottom	No (Retrofittable)	Textile	Aluminum	Anodized
20848-599	Front Panel without Handle	Hinged, Bottom	No (Retrofittable)	Textile	Aluminum	Anodized
20848-600	Front Panel without Handle	Hinged, Bottom	No (Retrofittable)	Textile	Aluminum	Anodized

Catalog Number	Type	Mounting	EMC Shielding	EMC Gasket Type	Material	Front Finish
20848-601	Front Panel without Handle	Hinged, Bottom	No (Retrofittable)	Textile	Aluminum	Anodized
20848-605	Front Panel without Handle	Hinged, Bottom	No (Retrofittable)	Textile	Aluminum	Anodized
20848-606	Front Panel without Handle	Hinged, Bottom	No (Retrofittable)	Textile	Aluminum	Anodized
20848-607	Front Panel without Handle	Hinged, Bottom	No (Retrofittable)	Textile	Aluminum	Anodized
20848-604	Front Panel without Handle	Hinged, Bottom	No (Retrofittable)	Textile	Aluminum	Anodized
20848-602	Front Panel without Handle	Hinged, Bottom	No (Retrofittable)	Textile	Aluminum	Anodized
20848-603	Front Panel without Handle	Hinged, Bottom	No (Retrofittable)	Textile	Aluminum	Anodized
20848-696	Front Panel without Handle	Hinged, Bottom	No (Retrofittable)	Textile	Aluminum	Anodized

Table 2/3						
Catalog Number	Rear Finish	Treated Edges	Rack Height	Height (H)	Rack Width	Width (W)
20848-608	Conductive	No	3U	128.4mm	28HP	141.9mm
20848-599	Conductive	No	3U	128.4mm	42HP	213mm
20848-600	Conductive	No	3U	128.4mm	63HP	319.7mm
20848-601	Conductive	No	3U	128.4mm	84HP	426.4mm
20848-605	Conductive	No	4U	172.9mm	42HP	213mm
20848-606	Conductive	No	4U	172.9mm	63HP	319.7mm
20848-607	Conductive	No	4U	172.9mm	84HP	426.4mm
20848-604	Conductive	No	6U	261.8mm	84HP	426.4mm
20848-602	Conductive	No	6U	261.8mm	42HP	213mm
20848-603	Conductive	No	6U	261.8mm	63HP	319.7mm
20848-696	Conductive	No	6U	261.8mm	28HP	141.9mm

Table 3/3			
Catalog Number	Complies With	Package Quantity	Finish
20848-608	IEC 60297-3-101, IEEE 1101.1/10	1	Anodized, Passivated
20848-599	IEC 60297-3-101, IEEE 1101.1/10	1	Anodized, Passivated

North America

All locations
+1.763.422.2661
Chat with us:
schroff.nvent.com

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
schroff.nvent.com

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
schroff.nvent.com

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
schroff.nvent.com



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER