

REPLACEMENT MODULE FOR DSD, 10 KA



CERTIFICATIONS




SPECIFICATIONS

Catalog Number	DSD110M275
Article Number	702566
Nominal System Voltage (Un)	220 - 240 V
Max Continuous Operating Voltage (Uc)	275 VAC 350 VDC
Nominal Discharge Current (In), Per Mode	5kA 8/20 μ s
Max Discharge Current (Imax), Per Mode	10kA 8/20 μ s
Voltage Protection Level (Up)	930 V @ 3 kA 1300 V @ 5 kA
Frequency	0 - 60 Hz
Technology	MOV with thermal disconnect
Enclosure Material	UL® 94V-0 Thermoplastic
Status Indication	Mechanical flag
Temperature	-40 to 80 °C
Module Width	1 M
Depth (D)	49mm

Catalog Number	DSD110M275
Height (H)	45 mm
Width (W)	18 mm
Unit Weight	0.07 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500