

CRIMPING COMPRESSION TOOL, MANUAL



FEATURES

Wide cross section range

Ergonomic design

Lightweight and easy to use

Includes easy-to-carry custom case

SPECIFICATIONS

Table 1/1

| Catalog Number | Article Number | System | Dies | Crimping Shape | Conductor Size |
|----------------|----------------|--------|--------------------------|----------------|--|
| M2M | 716900 | Manual | RKM2 series, PKM2 series | Hexagon | #10 Stranded - 600 kcmil Stranded, 6 mm ² Stranded - 300 mm ² Stranded |

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER