nVent
DATA-SOLUTIONS

CRIMPING COMPRESSION TOOL DIE, TYPE ML, HEAVY-DUTY DIN46235, #6 STRANDED-2/0 STRANDED, 16 MM² STRANDED-70 MM² STRANDED

CATALOG NUMBER

PKML1670

FEATURES

Suitable for cable lugs and connectors

PRODUCT ATTRIBUTES

Article Number: 716994

Lug/Connector Type: Heavy-Duty DIN46235

Conductor Size: #6 Stranded - 2/0 Stranded; 16 mm² Stranded - 70 mm² Stranded

Crimping Width: 5mm

Tool: MLB

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

© 2025 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners.

nVent reserves the right to change specifications without notice.