

## 19" FAN UNIT, 1 U, SPEED CONTROL AND MONITORING

Fan Unit for installation into a 1 U space within the Cabinet.



### CERTIFICATIONS



### FEATURES

Range selectable: 20 ... 40 °C and 30 ... 50 °C

Low noise through temperature dependent air flow

External sensor, max speed is default failure state

Function control with LEDs and via dry contact

Contact protection in accordance with DIN EN ISO 13857

### SPECIFICATIONS

Table 1/1

| Catalog Number | Input Voltage DC | Product Type | Input Voltage AC | Accessory Type | Certifications |
|----------------|------------------|--------------|------------------|----------------|----------------|
| 10713-098      | 24 V min         | Fan Unit     |                  | Fan unit, 19"  | RoHS, CE, EAC  |
| 10713-099      | 24 V min         | Fan Unit     |                  | Fan unit, 19"  | RoHS, CE, EAC  |
| 19713-006      |                  | Fan Unit     | 230 V min        | Fan unit, 19"  | RoHS, EAC      |
| 19713-121      |                  | Fan Unit     | 230 V min        | Fan unit, 19"  | RoHS, EAC      |

## **WARNING**

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:  
**nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF**  
**TRACER**