


TRC FOUR POLE DISTRIBUTION BLOCK, 630 A



CERTIFICATIONS



FEATURES

- Transparent protection cover
- Bolts included for output connections
- Easy accessibility for wiring
- Ready to use out of the box, saving installation time and labor
- RoHS compliant

SPECIFICATIONS

Table 1/3						
Catalog Number	Article Number	Peak Short Circuit Current (Ipk)	Material	Short Term Withstand Current (Icw) 1s	Line Side Number of Connections	Load Side Number of Connections
TRC-630A	563190	84kA	Copper, Glass Fibre Reinforced Polyamide, Plexiglass	52kA	1	8

Table 2/3

Catalog Number	Article Number	Thread Size (TS)	Max Working Voltage, IEC (Ui)	Hole Size (HS)	Height (H)	Width (W)
TRC-630A	563190	M8	1000	10mm	338 – 390mm	340mm

Table 3/3

Catalog Number	Article Number	Depth (D)	A	Unit Weight	Flammability Rating	Complies With
TRC-630A	563190	60mm	290mm	4.8kg	UL® 94V-0	IEC® 60439.1, IEC® 61439.1, IEC® 60695-2-11 (Glow Wire Test 960 °C)

ADDITIONAL PRODUCT DETAILS

Line side and load side number of connections are per pole.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER