


CABS BUSBAR SUPPORT KIT



CERTIFICATIONS



FEATURES

For all busbar types

Improve bending resistance by interlocking or stacking two profiles

Quick and easy to install

Halogen free insulators

RoHS compliant

SPECIFICATIONS

Table 1/3

Catalog Number	Article Number	Typical Application Current Rating	Busbars per Phase	Busbar Thickness	Busbar Width	Max Working Voltage, IEC (Ui)
CABS4-5TN-400	549310	400 – 4,500 A	1 – 4	5 mm	30 – 125 mm	1,000 VAC, 1,500 VDC


Table 2/3

Catalog Number	Article Number	Working Temperature	C	B	Width (W)	A
CABS4-5TN-400	549310	-40 to 130 °C	325 mm	75 mm	350 mm	300 mm

Table 3/3

Catalog Number	Article Number	Unit Weight
CABS4-5TN-400	549310	0.800 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:
nVent.com CADDY ERICO HOFFMAN RAYCHEM SCHROFF
TRACER